EF9M Series

LED




Features

- Fire-retardant thermoplastic
- 300° rotation
- CSA certified to C22.2 No. 141
- 6, 12 and 24V with various wattages
- Warranty details at: www.emergi-lite.ca

Dimensions

Dimensions are approximate and subject to change.



Typical specifications

Lamp head and stem shall be injection molded, impact resistant, flame retardant thermoplastic and shall require no tool for aiming or adjustment. The lens shall be inverse concave design and fully adjustable for aisle or area distribution during installation without the need to energize the lamp. Visual identification of distribution shall be provided through position of adjustment pins.

Fixture shall be supplied with a canopy for installation on any four inch octagon box. Housing shall be designed to allow for lamp replacement if required.

The remote unit shall be the Emergi-Lite® model: __

Wire guards

S i

Ordering code	Description
460.0029-E	Wall and ceiling mount

Replacement lamps

Ordering code	Lamp type	Voltage/wattage
580.0097-E	MR16 LED	6V-4W
580.0122-E	MR16 LED	6V-5W
580.0093-E	MR16 LED	12V-4W
580.0098-E	MR16 LED	24V-4W
580.0100-E	MR16 LED	24V-6W
580.0104-E	MR16 LED	12V-5W
580.0106-E	MR16 LED	12V-6W

Housing colour



Ordering information

Series	Number of lamps	Lamp type	Colour	Voltage/wattage	
EF9= mini, PAR 18 D= double head T= triple head	Blank= single head	M= MR16 LED	- B = black	-LA= MR16 LED, 6V-4W	
	D = double head		Blank= factory white	-LB= MR16 LED, 6V-5W	
			-LG= MR16 LED, 12V-4W		
				-LI= MR16 LED, 12V-5W	
				-LJ= MR16 LED, 12V-6W	
				-LL= MR16 LED, 24V-4W	
				-LM= MR16 LED, 24V-6W	

Example: EF9M-LM

.