### **STANPRO**

# N

## PAR18/MR16 MINI REMOTE

Plastic Construction Single, Double, Triple, or Quad 6V, 12V & 24V Lamps in LED, Quartz & Tungsten

The N series of commercial thermoplastic PAR18/MR16 remotes provides the perfect balance of value and performance. The heads are fully adjustable and both tilt and swivel are lockable. The standard canopy is designed to mount directly to typical electrical junction boxes. Available in 6V, 12V and 24V models, utilizing either LED, tungsten or quartz halogen lamps.

#### **FEATURES AND SPECIFICATIONS**

- UV stabilized, high impact thermoplastic, composite head construction
- Fully adjustable both tilt and swivel
- $-\ 5"$  diameter thermoplastic canopy standard
- Two surface canopy mounting holes designed to match standard electrical junction boxes
- White color is standard, black is optional
- Variety of lamp options:
  - 6VDC, 12VDC or 24VDC
  - Tungsten lamps
- Quartz halogen lamps
- LED lamps

Stanpro's LED current technology ensures the lumens output remains constant throughout the battery's discharge whether at 6V, 12V, or 24V applications.

#### Approval

- CSA Certified to C22.2 #141-15

#### • Compliance

- Meets requirements of ICES-005

Project:
Type:
Catalogue #:
Drawn by:
Date:



-	/ I \
-	

quick ship







LED fixture


ICES 005




# DIMENSIONS









#### **OVERVIEW**

Г		
	Light source	LED or Incandescent
	DC voltage	6VDC, 12VDC, 24VDC



#### **ORDERING GUIDE - LED**

N	_				,	
Series	Nbr of heads	Voltage	Wattage	Lamp type	Colour	Options†
N	1 - Single head 2 - Double head 3 - Triple head	06-12V - 6VDC to 12VDC operational	<b>3W -</b> 3 watts <b>4W -</b> 4 watts <b>5W -</b> 5 watts	LJ - LED	WH - White (standard) BK - Black	LCP, TP, WGD
	4 - Quad head (require 9.53"	12-24V - 12VDC to 24VDC operational	<b>6W -</b> 6 watts <b>7W -</b> 7 watts	LA - LED		
	dia. canopy)	<b>24V -</b> 24VDC	<b>4W -</b> 4 watts <b>5W -</b> 5 watts	LR - LED		

For detailed options descriptions, please consult the options page.

QUICK SHIP: Not all products are Quick Ship. To view our Quick Ship qualified products, please consult our Quick Ship Product Guide at stanprols.com/quick-ship-product-guide.

Product availability is subject to change without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.

#### PHOTOMETRY PERFORMANCE

LE	D	Lumen output	Im/W	CCT	Beam angle
3W	LJ	313	104lm/W	5000	20°
4W	LJ	330	82lm/W	5000	20°
5W	LJ	591	118lm/W	5000	28°
4W	LR	320	80lm/W	5000	24°
5W	LA	438	87lm/W	5000	24°
6W	LA	505	84lm/W	5000	24°
7W	LA	631	90lm/W	5000	24°

#### **SPACING GUIDE**

Mounting height	Spacing centre to centre (feet)						
	3WLJ 4WLJ 5WLJ 4WLR 5WLA 6WLA 7WL						
7 ft	78	83	97.5	76	95	108	126
10 ft	75	76	92.5	74	88	98	116
15 ft	66	68	82.5	60	76	85	102
20 ft	58	61	75	51	66	75	90

## Comments





#### **ORDERING GUIDE - INCANDESCENT**

N	_	_			/
Series	Nbr of heads	Voltage	Lamp	Colour	Options†
N	<ul><li>1 - Single head</li><li>2 - Double head</li><li>3 - Triple head</li><li>4 - Quad head (require 9.53" dia. canopy)</li></ul>	06V - 6VDC 12V - 12VDC 24V - 24VDC	See lamp selection chart below	WH - White (standard) BK - Black	LCP, WGD

† For detailed options descriptions, please consult the options page.

QUICK SHIP: Not all products are Quick Ship. To view our Quick Ship qualified products, please consult our Quick Ship Product Guide at stanprols.com/quick-ship-product-guide.

Product availability is subject to change without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.

#### **LAMP SELECTION - INCANDESCENT**

PAR18 • Small head						
6 volts 12 volts 24 volts						
Quartz halogen	08Q, 10Q	10Q, 12Q	12Q			
Tungsten	09T	9T	9T, 18T			

#### Comments



All products are subject to change or may be discontinued any time without notice.

