__

Utility boxes and covers



CI2018



CI2018-SB



BC2020



BC2020-R



BC20-C-1



BC20-C-3



BC20-C-4



BC20-C-5



	Volume	Features Bracket Raised Ground Screw			¹ / ₂ in. bottom	Knockouts
Cat. No.	(Cu. in.)			1/2 in. ends		1/2 in. sides
1 ¹ / ₂ in. deep – 4 in. x 2 ¹ / ₄ in.						
CI2018	13.0	_	no	2	2	6
CI2018-SB	13.0	"SB"	no	2	2	3
1 ⁷ /s in. deep – 4 in. x 2 ¹ /s in.						
BC2020	14.0	_	yes	2	2	6
BC2020-R	14.0	_	-	2	_	6

Cat. No.	Description
Covers - 20 Series	
BC20-C-1	For duplex receptacle
BC20-C-3	For 113/32 in. diameter 15 A single receptacle
BC20-C-4	Blank
BC20-C-5	For toggle switch

Note: BC2020-R can be installed on CI2018 / BC2020 Series

Covers: Device mounting screws included

Utility boxes and covers





















BC1110-SSX

BC1110-R

1151 (For toggle switch)

1198 (For Decora or GFCI)

(For duplex receptacle)



















BC11-C-4

BC11-C-5

CI11-C-10-HV

BC11-C-4-HV

BC11-C-5-HV



	Volume	Features				Knockouts
Cat. No.	(Cu. in.)	Bracket	Raised Ground Screw	1/2 in. ends	¹ / ₂ in. bottom	1/2 in. side:
1 ¹ / ₂ in. deep – 4 in. x 2 ¹ / ₄ in.				'		
CI1141	13.0	mounting ears	no	2	2	(
1 ⁷ / ₈ in. deep – 4 in. x 2 ³ / ₈ in.				'		
BC1110	16.5	_	yes	2	2	(
CI1110-SB	16.5	"SB"	yes	2	2	3
BC1110-R	16.5	-	-	2	_	(
BC1110-LSKO	16.5	_	yes	2	2	-
BC1110-SSX	16.5	"SSX"	yes	2	2	
2 1/8 in. deep – 4 in. x 2 1/2 in.				,		
1151*	18.5	=	yes	2	2	-
1198*	18.5	_	yes	2	2	-
1199*	18.5	_	yes	2	2	

^{*} cULus listed

Cat. No.	Description	Cat. No.	Description
Covers – 11 Series			
BC11-C-1	For duplex receptacle	BC11-C-10	Decora/GFCI
BC11-C-2	For 1 19/32 in. diameter 15 A single receptacle	CI11-C-10-HV	Decora 347 V
BC11-C-3	For 1 13/32 in. diameter 15 A single receptacle	BC11-C-4-HV	Blank 347 V
BC11-C-4	Blank	BC11-C-5-HV	For toggle switch
BC11-C-5	For toggle switch		

Note: Covers: Device mounting screws included