SATCO' NUVO

Project Name

Location

Prepared By



SATCO S39397 120W/LED/HID/5K/100-277V/EX39

Notes

General Status Active Watts 120 750 Incandescent Equivalent Fluorescent Equivalent 200 HID Equivalent 600 Volts 100V-277V Shape Corncob Base Mogul Extended ANSI Base EX39 Finish Clear CCT (Kelvin) 5000 Temperature Natural Light CRI 80 Lumens 17160 Beam Spread 300 Dimmable Non-Dimmable Hours Rated 50000 Lamp Type Corncob LED Technology Length: 17.32 in. Width: 9.25 in. Min Compartment Size Depth: 9.25 in. Ballast Bypass-Direct wire only 100-**Ballasting Requirements** 277V Electrical

Working Voltage	AC 100-277V
Operating Frequency	50/60 Hz
Power Factor	>0.9
Burning Position	Up or Down Operation Only
Surge Protection	Built-in surge protection - 6KV
Thermal Management	Hi-PRO lamps are manufactured with a new Thermal Management circuit design (Temperature Control).I
Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)
Physical	
MOL	10.34

MOL	10.34
MOD	4.72
Lens Finish	Clear
Lens Material	Plastic
Housing Color	White
Weight (lb.)	3.69

Additional Information

Additional Info	Approved for totally enclosed fixtures; Base up or base down operation; For outdoor & indoor use; Emits no UV light / Contains no Mercury (Hg)
Rated For Enclosed Fixture	Yes

Copyright 2020 Satco Products, Inc. All Rights Reserved For More Information Visit: <u>https://www.satco.com/</u>



wwj 11-09-2020 01:16:24

IP Rating	IP64
Shatter-Proof Type	Shatter resistant materials. Acceptable for use in food prep areas
Warranty	5 Year Limited - Hi-Pro
Compliance	
Safety Listing	cULus
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	PLP79G1HJHUF;PLZWRGQMT164
CEC Status	Lawful for sale in California
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Lamp

