EF26/EF26D/EF26DS Series

Surface mount remote fixtures



Features


- Cubic, vandal-resistant surface-mounted fixture
- Single, twin or double cube with center body
- Frosted polycarbonate cube
- CSA certified to C22.2 No. 141
- Warranty details at: www.emergi-lite.ca

Dimensions

REMOTE FIXTURES

Dimensions are approximate and subject to change.





Typical specifications

Remote heads **EF26/EF26DS/EF26D Series** shall be comprised of one (single) or two (double or twin) 12W adjustable heads with LED lamps. Each lamp shall be housed in an impactresistant polycarbonate cube. The cube lens shall be frosted to diffuse the light.

Heads shall provide mounting holes for installation on a standard octogonal box.


The remote unit shall be the **Emergi-Lite**[®] model: _____.

Wire guards

Ordering code	Description
460.0035-E	Wall mount (EF26)
460.0031-E	Wall mount (EF26D)
460.0032-E	Wall mount (EF26DS)

Replacement lamps

Ordering code	Lamp type	Voltage/wattage
580.0097-E	MR16 LED	6V-4W
580.0122-E	MR16 LED	6V-5W
580.0093-E	MR16 LED	12V-4W
580.0098-E	MR16 LED	24V-4W
580.0100-E	MR16 LED	24V-6W
580.0104-E	MR16 LED	12V-5W
580.0106-E	MR16 LED	12V-6W
580.0113-E	MR16 LED	120V-4W
580.0125-E	MR16 LED	120V-7W



Ordering information

Series	Lamp style	Colour	Options	Lamp style/wattage	
EF26= single cube EF26D= double cube EF26DS= twin cube	M = MR16	B = black Blank = factory white	Blank= no options TP= tamper-proof screws ¹	-LA= MR16 LED, 6V-4W -LB= MR16 LED, 6V-5W -LG= MR16 LED, 12V-4W -LI= MR16 LED, 12V-5W -LJ= MR16 LED, 12V-6W	-LL= MR16 LED, 24V-4W -LM= MR16 LED, 24V-6W -LW= MR16 LED,120V-4W -LX= MR16 LED, 120V-7W
Example: EF26M-LL			*690.0454-E= tamper-proof bit (sold separately)		

EMERGI-LITE