



## RK1942

by Burndy  
Catalog ID: RK1942

Prop65

Wire Mike, #6 - 336.4 (26/7) str. ACSR #18 str. - 2,000 kcmil #20 sol. - 4/0 sol., 4.38 in L, 1.52 in W.

- Strong, durable, high quality

Features: Provides Quick And Easy Identification Of Commonly Used Conductors (ACSR, Stranded And Solid AWG), Provides Quick And Easy Identification Of IPS Tubing And Rigid Conduit, Provides Quick And Easy Identification Of Thinwall Conduit, Measures I.D. And O.D. Of Tubing, Provides Easy Conversion Of Information, Strong, Durable, Long Lasting, High Quality Stainless Steel Wire Mike, Convenient Size Makes It Easy To Carry, Available With Your Company Name And Logo, Customer Must Supply Camera Ready Artwork, For Use On Thinwall Conduit: 3/8 - 2-1/2 IN, For Use On Tubing Sizes: 3-11/8 IN Inside Diameter X 2-15/16 IN Outside Diameter, For Use On Acsr: 6 AWG - 336.4 (26/7) KCMIL Stranded, For Use On Stranded: 18 AWG Stranded - 2000 KCMIL, For Use On Ips Tubing (cu/al) And Rigid Conduit: 1/4 - 2-1/2 IN, For Use On Solid: 20 - 4/0 AWG Solid

## Product Details

### General

Application	Grounding
Material	Vinyl, Textured
Sub Brand	ACCESSORY
Tool Type	WIRE MIKE COVER
Type	WIREMIKE
UPC	781810024409
UPC 12 Digit	7818100244099

### Dimensions

Length	4.38 in
Width	1.94 in

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

### Logistics

Minimum Pack Quantity	10
-----------------------	----

For further technical assistance, please contact us

**BURNDY Headquarters**

47 East Industrial Park Drive  
Manchester, New Hampshire 03109

**Customer Service Hours:**

8 AM - 8 PM Eastern Monday-Friday  
Emergency Service 24-hours/365 Days  
Phone: 1-800-346-4175  
1-603-647-5299 (International)