



4-1/4" Hole Dozer™ Bi-Metal Hole Saw

49-56-0223

★★★★★ Be the first to [Write a Review](#)

OVERVIEW

DETAILS

OPTIONS

REVIEWS

PHOTOS (3)

VIDEOS (0)



PRODUCT DETAILS

FEATURES

- ✓ Rip Guard™, the strongest tooth form in the industry
- ✓ Rip Guard™ Limited Lifetime Tooth Break Warranty
- ✓ Plug Jack™, an all access slot design for fast plug removal
- ✓ Bi-metal construction with 8% cobalt for increased wear resistance

SPECIFICATIONS

Hole Diameter	4-1/4"
Thread	5/8"-18
Depth of Cut	1-5/8"
RPM Mild Steel	80
RPM Stainless Steel	40
RPM Cast Iron	55
RPM Aluminum	120