## **JUNO**°

Project:		
Fixture Type:		
Location:		
Contact/Phone:		

# 4" MINIATURE UNIVERSAL TC REMODEL HOUSING

INCANDESCENT LAMPS

TC1R

#### **PRODUCT DESCRIPTION**

TC Housing for remodel application where back side of ceiling is not accessible • Installs through an opening in the ceiling from below • Secured in place by factory installed remodel springs • Design for use in non-insulated areas • If installed where insulation is present, the insulation must be pulled back 3" from all sides of the TC housing.

#### **PRODUCT SPECIFICATIONS**

Lamp Lamp ratings based on trim selected – see reverse.

**Socket** Detachable medium base porcelain with nickel-plated copper screw shell.

Trims Trim selection shown on reverse.

Labels U.L. listed for through-branch wiring, damp locations and IP ● Product thermally protected against improper use of lamps or insulation ● Union made ● UL Listed/CSA certified ● Trim No. 11, 12, 4101, 4102 and 4181 are wet location approved for covered ceiling applications ● Trims 14, 17 are wet location approved for covered ceiling applications, when used with outdoor rated lamps.

**Testing** All reports are based on published industry procedures; field performance may differ from laboratory performance.


Product specifications subject to change without notice.


#### **INSTALLATION**

Junction Box Pre-wired junction box, UL listed/CSA certified for through-branch wiring maximum 4 No. 12 AWG 90° C branch circuit conductors (2 in, 2 out) ● Junction box provided with removable access plate, (5) ½″ knockouts, (4) Non-metallic sheathed cable connectors and ground wire ● Knockouts equipped with pryout slots.

**Housing** TC housing, 22-gauge galvanized steel • Remodel springs accommodate up to a 1¹/s" ceiling thickness.

#### **DIMENSIONS**





4 3/8" CEILING CUTOUT

#### **ACCESSORIES**

Catalog No.	Description
GU10-WHIP	GU10 Socket Whip
SMPLT-4	4" Housing Locator

To order, specify catalog number

#### **PRODUCT CODES**

Catalog Number	Input Voltage	Lamp Rating (max.)
TC1R	120V	R14/R16/R20/PAR16/PAR20 (See reverse for max. trim rating)



## 4" MINIATURE UNIVERSAL TC REMODEL HOUSING

INCANDESCENT LAMPS

### TC1R

50W PAR20.

50W R20

Sauare Frosted Lens

GU10 Socket Whip

with Clear Center

#### **ROUND TRIMS/LAMPS**

_	Cat. No.	Description	Max. Lamp Rating		Cat. No.	Description	Max. Lamp Rating
	13-WH	2" Pinhole with Integral Shield	50W PAR20/R20		16-WH	Scoop Wall Wash with higher inner shield	25W R14/40W R16 intermediate screw base
	14B-WH ◆◆ 14B-SC ◆◆ 14B-ABZ ◆◆ 14B-BL ◆◆ 14W-WH ◆◆	Black Baffle Black Baffle Black Baffle Black Baffle White Baffle	50W PAR20/R20		446-WH	Scoop Adjustable	50W MR16, PAR16, ES16 GU10 (Requires GU10-WHIP)
	17C-WH ♦♦ 17G-WH ♦♦ 17B-WH ♦♦	Cone - Clear Alzak® Cone - Gold Alzak® Cone - Black Alzak®	50W PAR20/R20		4101-WH ♦ 4101-SC ♦ 4101-ABZ ♦	Beveled Dome Shower Beveled Dome Shower Beveled Dome Shower	50W PAR/R20
	17PT-SC ◆◆ 17W-WH ◆◆ 17HZ-WH ◆◆ 17WHZ-WH ◆◆	Cone - Pewter Alzak® Cone - Gloss White Cone - Haze Cone - Wheat Haze			4102-WH ♦ 4102-SC ♦ 4102-ABZ ♦	Beveled Shower Beveled Shower Beveled Shower	50W PAR/R20
	17WHZ-ABZ ◆◆ 10-WH 10-BL	Cone - Wheat Haze  Push-In Flush Gimbal Ring  Push-In Flush Gimbal Ring	50W PAR20/ 75W ES20 GU10		4103FROST-WH 4103FROST-SC	Beveled Cylinder Beveled Cylinder	50W PAR/R20
	10-SC 10-ABZ	Push-In Flush Gimbal Ring Push-In Flush Gimbal Ring	(Requires GU10-WHIP)		4104HZ-SC 4104WHZ-ABZ	Beveled Cone Beveled Cone	50W PAR/R20
	18-WH 18-SC	Mini Eyeball Mini Eyeball	60W PAR16		4150MESH-SC	Cylinder	50W PAR/R20
	19-WH	Mini Eyeball	25W R14/40W R16 intermediate screw base		4180FROST	Solid Glass Collar	50W PAR/R20
	440-WH 440-BL 440-SC 440-ABZ	Flush Gimbal Ring Flush Gimbal Ring Flush Gimbal Ring Flush Gimbal Ring (New tighter gap, uses 2° optical media)	50W MR16, PAR16, ES16 GU10 (Requires GU10-WHIP)		4181CLEAR ◆	(torsion spring attachment)  All Glass Shower (torsion spring attachment)	50W PAR/R20
	445-WH	Slot Aperture Downlight or Adjustable	50W MR16, PAR16, ES16 GU10	SQUAR	RE TRIMS/LAMP	S	
			(Requires GU10-WHIP)		Cat. No.	Description	Max. Lamp Rating
	448-WH 448-SC	Eyeball with Black Baffle Eyeball with Black Baffle	50W MR16, PAR16, ES16 GU10 (Requires GU10-WHIP)		17SQ-HZ-WH ◆◆ 7 17SQ-W-WH ◆◆ 17SQ-B-WH ◆◆ 17SQ-WHZ-WH ◆◆	Square Downlight	50W PAR20, 30W R20
	11-WH ◆	Drop Opal	50W PAR20/R20		7 135Q−WH	Square Pinhole	50W PAR20, 50W R20
	12W-WH ◆ 12W-SC ◆ 12W-ABZ ◆	Shower Trim, frosted perimter lens Shower Trim, frosted perimter lens Shower Trim, frosted perimter lens	50W PAR20/R20	401/	440SQ-WH 440SQ-BL	Square Flush Gimbal	50W MR16 120V GU10 Base (Requires GU10-WHIP) 35° Vertical Adjustment

Trim Size: 5" O.D.

Trim Finish: ABZ - Classic Aged Bronze, BL - Black, GP - Graphite, PW - Plastic White (Polycarbonate material shower trim),

SC - Satin Chrome, SL - Silver, WH - White.

Alzak is a registered trademark of Alcoa Corp.

Note: In Canada when insulation is present, Type IC fixtures must be used.

- ◆ UL Listed for use in wet location.
- ◆◆ UL Listed for use in wet location with outdoor rated lamp.



GU10-WHIP