

TECK90 - 600 V



Part ID	Size & # Cdrs.	Core Diameter		Armour Diameter		Overall Diameter		Cable Weight*	
		Inches	mm	Inches	mm	Inches	mm	lbs/1000'	kg/km
#14 AWG									
800432	2C	0.361	9.2	0.542	13.8	0.630	16.0	195	290
800453	3C	0.381	9.7	0.562	14.3	0.646	16.4	216	322
800467	4C	0.416	10.6	0.616	15.6	0.700	17.8	255	380
800476	5C	0.454	11.5	0.654	16.6	0.738	18.7	286	425
800480	6C	0.494	12.5	0.694	17.6	0.778	19.8	306	456
800484	7C	0.494	12.5	0.694	17.6	0.778	19.8	333	496
800488	8C	0.565	14.4	0.765	19.4	0.849	21.6	389	579
800410	10C	0.657	16.7	0.857	21.8	0.941	23.9	466	694
800415	12C	0.677	17.2	0.877	22.3	0.961	24.4	497	739
800418	15C	0.750	19.1	1.000	25.4	1.084	27.5	628	935
800421	20C	0.871	22.1	1.121	28.5	1.205	30.6	794	1,181
800425	25C	0.963	24.5	1.213	30.8	1.297	32.9	921	1,370
800446	30C	1.017	25.8	1.267	32.2	1.351	34.3	1,031	1,535
#12 AWG									
800429	2C	0.399	10.1	0.580	14.7	0.664	16.9	224	333
800450	3C	0.422	10.7	0.597	15.2	0.681	17.3	257	382
800504	4C	0.461	11.7	0.661	16.8	0.745	18.9	295	439
800475	5C	0.505	12.8	0.705	17.9	0.789	20.0	335	498
800479	6C	0.581	14.8	0.781	19.8	0.865	22.0	398	592
800483	7C	0.581	14.8	0.781	19.8	0.865	22.0	424	631
800487	8C	0.628	16.0	0.828	21.0	0.912	23.2	468	697
800409	10C	0.733	18.6	0.933	23.7	1.017	25.8	563	838
800414	12C	0.756	19.2	1.006	25.6	1.090	27.7	665	989
800417	15C	0.879	22.3	1.129	28.7	1.213	30.8	820	1,220
800420	20C	0.972	24.7	1.223	31.1	1.306	33.2	990	1,474
800424	25C	1.077	27.4	1.327	33.7	1.411	35.8	1,165	1,733
800445	30C	1.139	28.9	1.389	35.3	1.473	37.4	1,335	1,987
#10 AWG									
800427	2C	0.453	11.5	0.653	16.6	0.743	18.9	281	418
800448	3C	0.480	12.2	0.680	17.3	0.770	19.6	329	489
800463	4C	0.556	14.1	0.756	19.2	0.846	21.5	405	602
800474	5C	0.608	15.4	0.808	20.5	0.898	22.8	462	687
800477	6C	0.662	16.8	0.862	21.9	0.952	24.2	520	774
800482	7C	0.662	16.8	0.862	21.9	0.952	24.2	560	833
800486	8C	0.717	18.2	0.917	23.3	1.007	25.6	622	925
800408	10C	0.825	21.0	1.075	27.3	1.165	29.6	843	1,255
800413	12C	0.918	23.3	1.168	29.7	1.258	32.0	930	1,384
800416	15C	1.006	25.6	1.256	31.9	1.346	34.2	1091	1,624
800419	20C	1.115	28.3	1.365	34.7	1.455	37.0	1337	1,990
800423	25C	1.239	31.5	1.489	37.8	1.579	40.1	1599	2,379
800444	30C	1.293	32.8	1.543	39.2	1.627	41.3	1814	2,700

* Weights are based on Aluminum Armour