

Designed with simplicity in mind, the BU2 range hood models are made to exacting standards and offer the most for the money.

SIZE	WHITE	WHITE WITH BLACK CONTROL	BLACK	STAINLESS	GREASE FILTER (replacement)	CHARCOAL FILTER
24 in.	-	BU224WH	-	BU224SS	BP29	41F
30 in.	BU230WW	BU230WH	BU230BL	BU230SS	BP29	41F

PERFORMANCE

Duct Orientation	Size	Damper	Sones on high speed	CFM on high speed
Vertical - Rectangular	3¼ in. x 10 in.	Included	6.5	160
Horizontal - Rectangular	3¼ in. x 10 in.	Included	6.5	160

FEATURES

Control type	2-speed rocker switch
Delay off	no
Filter Clean Reminder	no
Heat Sentry™	no
Lighting	1-level 75-watt bulb (not included)
Grease Filter	Aluminum (Qty. 1)
ENERGY STAR®	no
Recirculation	Charcoal filter sold separately

AC INPUT

120 V, 60 Hz - 2.5 AMPS

OPTIONAL ACCESSORIES

3¼ in. x 10 in. to 6-in. Round Duct Transition	411
7-in. Round Damper	BP87
7-in. Round Adapter Plate	SR680508

MOUNTING HEIGHT

18 in. to 24 in. from cooktop to bottom of hood

LIMITED WARRANTY

1-year
(See installation manual for full warranty text.)

FOR INDOOR USE ONLY

