

## SHOCKWAVE™ IMPACT DUTY SETS



<b>15 Pc SHOCKWAVE™ 1" Insert Bit Phillips #2 Set</b> 48-32-5003	<b>15 Pc SHOCKWAVE™ 2" Power Bit Phillips #2 Set</b> 48-32-5004	<b>10 Pc SHOCKWAVE™ 1" Square Recess Insert Bit #2 Set</b> 48-32-5008	<b>25 Pc SHOCKWAVE™ 1" Insert Bit Phillips #2 Set</b> 48-32-5009	<b>10 Pc SHOCKWAVE™ 1" Square Recess Insert Bit Phillips #2 Set</b> 48-32-4607
<b>Includes:</b> <ul style="list-style-type: none"> <li>■ (15) 1" Phillips #2 (Gravity Feed Merchandiser)</li> </ul>	<b>Includes:</b> <ul style="list-style-type: none"> <li>■ (15) 2" Phillips #2 (Gravity Feed Merchandiser)</li> </ul>	<b>Includes:</b> <ul style="list-style-type: none"> <li>■ (10) 1" Square Recess #2 (Gravity Feed Merchandiser)</li> </ul>	<b>Includes:</b> <ul style="list-style-type: none"> <li>■ (25) 1" Phillips #2</li> <li>■ (1) SHOCKWAVE™ 2.36" Magnetic Bit Tip Holder</li> </ul>	<b>Includes:</b> <ul style="list-style-type: none"> <li>■ (10) 1" Square Recess #2 (PDQ Tray Merchandiser)</li> </ul>



<b>25 Pc SHOCKWAVE™ 1" Insert Bit Phillips #2 Set</b> 48-32-4604	<b>12 Pc SHOCKWAVE™ Drive Guide Set</b> 48-32-4507	<b>22 Pc SHOCKWAVE™ Puck (10 per Tube)</b> 48-32-4011	<b>22 Pc SHOCKWAVE™ Puck</b> 48-32-4012
<b>Includes:</b> <ul style="list-style-type: none"> <li>■ (25) 1" Phillips #2 (PDQ Tray Merchandiser)</li> </ul>	<b>Includes:</b> <ul style="list-style-type: none"> <li>■ 1" ECX™ Bits: (1) ECX #1, (1) ECX #2</li> <li>■ 1" Phillips Bits: (1) PH #2, (1) PH #3</li> <li>■ 1" Slotted Bits: (1) SL 1/4", (1) SL 3/16"</li> <li>■ 1" Square Bits: (1) SQ #2</li> <li>■ 1" TORX® Bits: (1) TX15, (1) TX20, (1) TX25</li> <li>■ (1) SHOCKWAVE™ 3" Magnetic Drive Guide</li> <li>■ (1) Drive Guide Case</li> </ul>	<b>Includes:</b> <ul style="list-style-type: none"> <li>■ 1" Slotted Bits: (1) SL 1/8", (1) SL 3/16", (1) SL 1/4", (1) SL 9/32"</li> <li>■ 1" Phillips Bits: (1) PH #1, (3) PH #2, (2) PH #3</li> <li>■ 1" Square Bits: (1) SQ #1, (3) SQ #2, (1) SQ #3</li> <li>■ 1" TORX® Bits: (1) TX10, (1) TX15, (1) TX20, (1) TX25, (1) TX27, (1) TX30</li> <li>■ (1) SHOCKWAVE™ 2.36" Magnetic Bit Holder (Gravity Feed Merchandiser)</li> </ul>	<b>Includes:</b> <ul style="list-style-type: none"> <li>■ 1" Slotted Bits: (1) SL 1/8", (1) SL 3/16", (1) SL 1/4", (1) SL 9/32"</li> <li>■ 1" Phillips Bits: (1) PH #1, (3) PH #2, (2) PH #3</li> <li>■ 1" Square Bits: (1) SQ #1, (3) SQ #2, (1) SQ #3</li> <li>■ 1" TORX® Bits: (1) TX10, (1) TX15, (1) TX20, (1) TX25, (1) TX27, (1) TX30</li> <li>■ (1) SHOCKWAVE™ 2.36" Magnetic Bit Holder (PDQ Tray Merchandiser)</li> </ul>



<b>18 Pc SHOCKWAVE™ Driver Bit Set</b> 48-32-4403	<b>26 Pc SHOCKWAVE™ Drive and Fasten Set</b> 48-32-4408	<b>29 Pc SHOCKWAVE™ Driver Bit Set</b> 48-32-4401	<b>35 Pc SHOCKWAVE™ Drill and Drive Set</b> 48-32-4402
<b>Includes:</b> <ul style="list-style-type: none"> <li>■ Phillips Bits: 1" - (1) PH #1, (1) PH #2, (1) PH #3; 2" - (2) PH #2, (1) PH #3; 3-1/2" - (1) PH #2</li> <li>■ Slotted Bits: 1" - (1) SL 1/4", (1) SL 3/16"</li> <li>■ Square Bits: 1" - (1) SQ #1, (1) SQ #2; 2" - (2) SQ #2, (1) SQ #3; 3-1/2" - (1) SQ #2</li> <li>■ TORX® Bits: 2" - (1) TX15, (1) TX20</li> <li>■ (1) Case with Bulk Storage Container</li> <li>■ (1) SHOCKWAVE™ Magnetic Bit Holder</li> </ul>	<b>Includes:</b> <ul style="list-style-type: none"> <li>■ Phillips Bits: 1" - (1) PH #1, (3) PH #2, (1) PH #3; 2" - (1) PH #2</li> <li>■ Square Bits: 1" - (1) SQ #1, (2) SQ #2, (1) SQ #3; 2" - (1) SQ #2</li> <li>■ TORX® Bits: 1" - (2) TX20, (2) TX25, (1) TX30; 2" - (1) TX20, (1) TX25</li> <li>■ Slotted Bits: 1" - (1) SL 3/16"</li> <li>■ (1) 1/4" Hex to 3/8" Square Adapter</li> <li>■ Magnetic Nut Drivers: (1) 1/4", (1) 3/8", (1) 5/16"</li> <li>■ 3/8" Drives: (1) 1/2" Socket, (1) 9/16" Socket</li> <li>■ (1) SHOCKWAVE™ Compact Magnetic Bit Holder</li> </ul>	<b>Includes:</b> <ul style="list-style-type: none"> <li>■ Phillips Bits: 1" - (1) PH #1, (7) PH #2, (2) PH #3; 2" Power - (2) PH #2, (1) PH #3</li> <li>■ Square Bits: 1" - (1) SQ #1, (4) SQ #2, (1) SQ #3; 2" Power - (2) SQ #2</li> <li>■ Torx® Bits: 1" - (1) TX15, (1) TX20, (1) TX25; 2" Power - (1) TX25</li> <li>■ Magnetic Nut Drivers: (1) 1/4" Red, (1) 5/16" Amber, (1) 3/8" Blue</li> <li>■ Magnetic Bit Holder</li> <li>■ Case with Bulk Storage Container</li> </ul>	<b>Includes:</b> <ul style="list-style-type: none"> <li>■ Phillips Bits: 1" - (1) PH #1, (2) PH #2, (1) PH #3; 2" - (1) PH #2, (1) PH #3; 3-1/2" - (1) PH #2</li> <li>■ Square Bits: 1" - (1) SQ #1, (2) SQ #2, (1) SQ #3; 2" - (1) SQ #1, (1) SQ #2, (1) SQ #3; 3-1/2" - (1) SQ #2</li> <li>■ 1" ECX™ Bits: (1) ECX #1, (1) ECX #2</li> <li>■ 1" Slotted Bits: (1) SL 1/8", (1) SL 3/16", (1) SL 1/4"</li> <li>■ 2" TORX® Bits: (1) TX15, (1) TX20, (1) TX25, (1) TX30</li> <li>■ (1) 1/4" Hex to 3/8" Square Adapter; (1) 1/4" Hex to 1/2" Square Adapter</li> <li>■ Compact Magnetic Bit Holder</li> <li>■ Impact Drill Bits: (1) 7/32", (1) 1/4", (1) 1/8", (1) 5/32", (1) 3/16"</li> <li>■ 7/8" Impact Magnetic Nut Drivers: (1) 1/4", (1) 5/16", (1) 3/8"</li> </ul>

## STANDARD DRIVING BIT SETS



<b>21 Pc Driver Bit Set</b> 48-32-0221	<b>21 Pc Drive Guide Set</b> 48-32-1700	<b>38 Pc QUIK-LOK™ Drill and Drive Set</b> 48-32-1500	<b>40 Pc Drive Guide Set</b> 48-32-1505
---	--	--	--

# CARBIDE BITS

## SDS+ THIN WALL CARBIDE TIPPED CORE BITS



Size	Depth	Core Body w/ Guide Plate & Centering Pin*	8" SDS+ Adapter Shank	12" SDS+ Adapter Shank	7-1/2" Extension	Replacement Guide Plate	Replacement Centering Pin
1"	3-3/16"	48-20-5005*	48-03-3545	48-03-3551	48-95-6070	-	-
1-1/8"	3-3/16"	48-20-5010*	48-03-3545	48-03-3551	48-95-6070	-	-
1-1/4"	3-3/16"	48-20-5015	48-03-3545	48-03-3551	48-95-6070	48-20-6151	48-20-6150
1-3/8"	3-3/16"	48-20-5020	48-03-3545	48-03-3551	48-95-6070	48-20-6152	48-20-6150
1-1/2"	3-3/16"	48-20-5025	48-03-3545	48-03-3551	48-95-6070	48-20-6153	48-20-6150
1-3/4"	2-13/16"	48-20-5030	48-03-3555	48-03-3561	48-95-6075	48-20-6156	48-20-6155
2"	2-13/16"	48-20-5035	48-03-3555	48-03-3561	48-95-6075	48-20-6157	48-20-6155
2-1/2"	2-13/16"	48-20-5040	48-03-3555	48-03-3561	48-95-6075	48-20-6158	48-20-6155
3"	2-13/16"	48-20-5045	48-03-3555	48-03-3561	48-95-6075	48-20-6159	48-20-6155
3-1/2"	2-13/16"	48-20-5050	48-03-3555	48-03-3561	48-95-6075	48-20-6160	48-20-6155
4"	2-13/16"	48-20-5055	48-03-3555	48-03-3561	48-95-6075	48-20-6161	48-20-6155

\*Guide plate and centering pin not included with 1" & 1-1/8" diameter core bits

## SDS-MAX AND SPLINE THICK WALL CARBIDE TIPPED CORE BITS



	Size	Depth	Core Body w/ Guide Plate & Centering Pin	12" SPLINE Adapter Shank	18" SPLINE Adapter Shank	12" SDS-MAX Adapter Shank	18" SDS-MAX Adapter Shank	7-1/2" Extension	Replacement Guide Plate	Replacement Centering Pin
THICK WALL	1-1/2"	4-1/16"	48-20-5125	48-03-3564	48-03-3565	48-03-3572	48-03-3573	48-95-6085	48-20-5168	48-20-5199
	1-3/4"	4-1/16"	48-20-5130	48-03-3564	48-03-3565	48-03-3572	48-03-3573	48-95-6085	48-20-5169	48-20-5199
	2"	4-1/16"	48-20-5135	48-03-3564	48-03-3565	48-03-3572	48-03-3573	48-95-6085	48-20-5170	48-20-5199
	2-1/2"	4-1/16"	48-20-5140	48-03-3564	48-03-3565	48-03-3572	48-03-3573	48-95-6085	48-20-5171	48-20-5199
	3"	4-1/16"	48-20-5145	48-03-3564	48-03-3565	48-03-3572	48-03-3573	48-95-6085	48-20-5172	48-20-5199
	3-1/2"	4-1/16"	48-20-5150	48-03-3564	48-03-3565	48-03-3572	48-03-3573	48-95-6085	48-20-5173	48-20-5199
	4"	4-1/16"	48-20-5155	48-03-3564	48-03-3565	48-03-3572	48-03-3573	48-95-6085	48-20-5174	48-20-5199
	5"	4-1/16"	48-20-5160	48-03-3564	48-03-3565	48-03-3572	48-03-3573	48-95-6085	48-20-5175	48-20-5199
THIN WALL	5"	2-13/16"	48-20-5060	48-03-3540	-	48-03-3574	-	48-95-6075	48-20-6162	48-20-6155
	6"	2-13/16"	48-20-5065	48-03-3540	-	48-03-3574	-	48-95-6075	48-20-6163	48-20-6155