





Stainless Steel Sealing Rings

Cat. No.	Description
MSR-C2	Stainless steel sealing ring, tamper-proof

Polycarbonate Sealing Ring

Cat. No.	Description
S102WD	Ring, available with any meter socket

When ordering any meter socket, add suffix "Z" to meter socket cat. no. to exchange standard stainless steel ring for S102WD model.



Meter Protectors

Product Specifications

- Meter protector for use in problem areas (trailer parks, playgrounds, conservation areas)
- Steel construction (16 ga. galv. steel)
- Clear, unbreakable polycarbonate front cover, which allows full view of meter revenue reading and serial number
- Sealing and padlocking provision
- Grey painted

Cat. No.	Description
MP01	7-1/6 in. dia. x 4-3/4 in. deep for use with single phase residential meters
MP02	7-1/6 in. dia. x 8-3/4 in. deep for use with all meters, other than single phase residential meters





BS087 / BS089 / BS090



CM-BS100









Blank Meter Cover Plates

Oot No	Description
Cat. No.	Description
BS087	Grey ABS
BS089	Plastic "throw-away" cover
BS090	Clear unbreakable polycarbonate

Not recommended as a permanent cover for energized meter sockets.

Jumper Bar



Cat. No.	Description
CM-BS100	200 A Max.

Mast Coupler



Cat. No.	Description
MH200	Fits all sockets with regular 2-1/2 in. hub opening

Mast Hubs



Cat. No.	PVC Cat. No.	A Hub Size (in.)	В
MH10X	_	1	
MH12X	E991G	1-1/4	For 2-1/2 in. regular hub opening
MH15	E991H	1-1/2	(add hub adapter plate BS052 if used
MH20	E991J	2	with units having 4 in. hub openings)
MH25	E991K	2-1/2	
MH30	_	3	
MH35	_	3-1/2	For 4 in. hub opening
MH40	<u> </u>	4	

Supplied with 4 Robertson head screws.

Hub Adapter Plate



Cat. No.	Description
BS052	Permits use of regular size hubs on larger hub openings













Consist of thermoplastic insulators with jaws and connectors assembled for replacement of one meter socket

Accessories

Hub Opening Closure Plates



Cat. No.	Description
BS051	Inside attachment for regular hub opening (i.e.: 1 in. to 2-1/2 in.)
BS054	Inside attachment for larger hub opening (i.e.: 3 in. to 4 in.)

Insulated Neutral Kits



Cat. No.	Description
IN1000BA, IN1000BE, IN1000PL	100 A Max.
IN2000BS, IN2000PL	200 A Max.

Specify socket upon ordering.

Insulated Neutral Kit



Cat. No.	Description
IN4000JS	400 A Max. (JS4)

Ground Lug On Neutral Kit

Cat. No.	Description
GN2000	200 A Max. for BQ2, BS2 Series

Identification Marker Kits

Cat. No.	Description	Markers Kit Includes	Qty.
MINI-ID-KIT	Plastic case	Stainless steel markers of each numbers 0 thru 9 (dash + service)	10
MICRO-ID-KIT	Blue metal	Stainless steel markers of each letters A thru D	10
		Stainless steel markers of each numbers 0 thru 9	
		Words "SERVICE"	
	carrying case	CM-BS100 Jumper Bar 200 A Max.	4
		LS500 Meter Jaw Safety Shroud	10

Supplied with 4 Robertson head screws.

Identification Markers

Cat. No.	Description
No. 0 through No. 9	Clipped to the upper lip of the enclosure; provides permanent customer identification.
No. A through No. Z	Packed and sold in polyethylene bags of 10 identical markers except "SERVICE" which
No. SERVICE	has 7 individual letters





Ready-to-install replacement block assemblies



Cat. No.	Description
ВАЗ-Х	Fits BA3 / BE1 Series
A 1.1 - CC	and the second s

Add suffix "B" to cat. no. above if mounting bridge is required



Cat. No.	Description	
BS2-X-UNI	Fits BQ2 / BS2 Series uni block	
Add off "Dille of the off or all of the dille of the dill		

Add suffix "B" to cat. no. above if mounting bridge is required



Cat. No.	Description
BS2-XBGN-UNI	Neutral 200 A

Add suffix "B" to cat. no. above if mounting bridge is required $% \left(A^{\prime }\right) =A^{\prime }$



Cat. No.	Description
MO2-X-UNI	Fits MO2 Series uni block
A	

Add suffix "B" to cat. no. above if mounting bridge is required



Cat. No.	Description	
PL17X	Neutral 200 A	

Add suffix "B" to cat. no. above if mounting bridge is required



Cat. No.	Description
PL27-XEB	Fits PL27 Series uni block

Add suffix "B" to cat. no. above if mounting bridge is required





Repair Kits

Replacement Part Kits

Cat. No.	For Meter Socket	Component*
REPAIR KIT BE1-TCV	BE1-TCV	BS2027, CDA110, BONDLUG2, SCREW-BS1002
REPAIR KIT BQ2-V	BQ2-V	BS2027, BS2611L, BONDLUG2, SCREW-BS2402
REPAIR KIT BQ2-VGN	BQ2-VGN	BS2027, BS2411GN, BONDLUG2, SCREW-BS2402
REPAIR KIT BS2-TCV	BS2-TCV	BS2027, BS2611L, BONDLUG2, SCREW-BS2402
REPAIR KIT BS2-TCVBC	BS2-TCVBC	BS2027, BS2611L, NA75Z-3, SCREW-BS2402
REPAIR KIT MO2V/VO	M02V/V0	BS2027, BS8608, BONDLUG2, SCREW-BS2402

You can also order the components separately

Bond Lug

Cat. No.	Description
BONDLUG2-FG	Bond lug to be used in BE1,BQ2,BS2,MO2
NA75Z-3-FG	Bond lug to be used in BS2-TCVBC

Neutral Lug

Cat. No.	Description
BS8608-FG	Neutral for MO2 200 A
CDA110-FG	Neutral for BE1 100 A

Shroud

Cat. No.	Description
BS2027-FG	Red meter jaw safety shroud

Set Screw

Cat. No.	Description
SCREW-BS1002-FG 100A	Set screw only for 100 A lugs
SCREW-BS2402-FG 200A	Set screw only for 200 A lugs

Neutral

Cat. No.	Description
BS2611L-FG	Neutral 200 A
BS2411GN-FG	Neutral 200 A C/W Ground





BS8608-FG









SCREW-BS2402-FG 200A











^{*} Each part comes in a bag of 10
Easy to reorder. Simply add suffix **-FG** to the components listed in the kit.

Fifth Jaw Assemblies



Meter Socket Series	Standardcapacity 9 o' position	Full ca 9 o' po	pacity sition	Full capacity 6 o' position		
	C205	Z105*	Z205*	CM-B106*	B306*†	
BA3	•	•				
BDC	•		•		•	
BE1	•	•		•		
BE2	•	•				
BEC	•	•				
BD2	•		•		•	
BQ2	•		•		•	
BS2 / BS2L	•		•		•	
BS4 / BSC4	•		•		•	
C01	•	•		•		
C02	•		•		•	
CO1 Multigang	•	•		•		

^{*} CSA not applicable † For mono blocks only

Pole Mount Bracket Kit

Cat. No.	Description	Conductor Range	Use w/Series	Option 1	Option 2
PMB200	Secures Microlectric meter socket to a wooden pole via Option 1 or 2	14-2 AWG	BA3, BE1, BQ2, BS, CL, CO1, CO2, CT, MO2, PL17, PL27, VT	Use a lag bolt through 5/8 in. center keyhole	Use the two side bracket mounting holes (0.320 in. dia.) to wrap around the pole

Suitable for any Microlectric meter socket with mounting holes 5 in. apart. Attach meter socket using one or two bracket(s). PMB200 kit comes complete with 2 brackets, 1 ground connector. Includes assembly hardware.

Pole Mounting Kit

Cat. No.	Kit Includes	Qty.
PMBJS4	Support hangers	2
	1/2 in. x 4 in. lag bolt	1
	3/8 in. x 3 in. lag bolt	4
	5/16 in. x 1 in. carriage bolts, nuts and lock washers	4




Fifth Jaw Assemblies





Pole Line Hardware

Cat. No.	Description	F Dia. (in.)	G Dia. (in.)	H Dia. (in.)	T Thick (in.)	Weight (100 pcs)		Chd Dies
Gal. No.	Description					lb.	kg	Std. Pkg.
RC729	Square washer	5/8	2	_	3/16	22	10.0	400
BC301L	Carriage bolt	3/8	1-1/2	1-1/2		11	5.0	
B0506	Oval eye bolt		6	3		122	55.4	
B0508		F/0	8	4	_	136	61.8	50
B0510		5/8	10	4		150	68.1	
B0512			12	4		168	76.3	



CO3417M-1-FG





CO3009-KIT CO3009SD-KIT CO3409FB-KIT



BP250



CIEFA-1/2 / CIEFA-4 CIEFSA-1/2 / CIEFSA-4

KO Configuration					
000					
1/2 in.	3/4 in 1-1/4 in.				
1-1/2 in., 2 in.	2 -1/2 in., 4 in.				

Accessories

Breaker Mounting Bracket

Cat. No.	Description
C03417M-1-FG	Adjustable Mounting Bracket for CO2 Series to adapt to Siemens, SD and Cutler Hammer breakers

Flexible Braid and Conductor Kits

Cat. No.	Description
CO2FB-KIT	Connection wires adaptor kit for CO2 Series meter sockets for field installation. To be used with Cutler Hammer breakers
C03009-KIT	Siemens breaker conductor kit (breakers not included)
C03009SD-KIT	Square D breaker conductor kit (breakers not included)
CO3409FB-KIT	Eaton breaker flexible braid kit (breakers not included)

Connector Kit

Cat. No.	Description
BP250	Connector kit 2 x 250 kcmil

Service Entrance Heads

Cat. No.	Cat. No. Trade Size				
Service Entrance Heads (Cast Aluminum) Rigid Conduit					
CIEFA-1/2	1/2				
CIEFA-3/4	3/4				
CIEFA-1	1				
CIEFA-1 1/4	1-1/4				
CIEFA-1 1/2	1-1/2				
CIEFA-2	2				
CIEFA-2 1/2	2-1/2				
CIEFA-3	3				
CIEFA-3 1/2	3-1/2				
CIEFA-4	4				

Trade	KO Dimensions					
Size	Small	Large	Center			
1/2	0.312	_				
3/4	0.375	0.400				
1	0.400	0.500	_			
1-1/4	0.438	0.625				
1-1/2	0.610	0.750	0.400			

Cat. No.	Trade Size		
Service Entrance Heads (Cast Aluminum) E.M.T.			
CIEFSA-1/2	1/2		
CIEFSA-3/4	3/4		
CIEFSA-1	1		
CIEFSA-1 1/4	1-1/4		
CIEFSA-1 1/2	1-1/2		
CIEFSA-2	2		
CIEFSA-2 1/2	2-1/2		
CIEFSA-3	3		
CIEFSA-3 1/2	3-1/2		
CIEFSA-4	4		

Trade Size	KO Dimensions			
	Small	Large	Center	
2	0.750	1.000	0.525	
2-1/2	0.875	1.300	1.000	
3				
3-1/2	1.125	1.750	1.125	
4				