

Pass & Seymour

Lighting & Fan Controls Titan™ Series //Magnetic Low Voltage/Fan

Incandescent/Magnetic Low Voltage/Fan

CD Series, CD-P Series, CDLV Series, CDLV-P Series, CDSC Series, CDDH16, CDADAPTORKIT

A complete solution for easy, economical multi-gang installations

ultiple commercial controls in a ganged box? It's easy with P&S Titan Series: Superior quality, energy-efficient lighting control with a customizable multi-gang wall plate system and a high-end voltage adjustment feature. Includes an exclusive labeling system.

This complete product line offering features a rugged, more convenient, better-looking multi-gang installation.



Features & Benefits

Included screwless wall plate components make it easy to assemble a custom multi-gang wall plate in any configuration – saving money and time.

High reliability design with built-in surge and static protection plus oversize output devices to stand up to abuse.

Higher wattage ratings and minimal or no derating for faster job planning.

Built-in label holder enables instant circuit indentification; looks clean and professional. Power-failure memory retains presets through power outages.

Preset models feature large ON/OFF button and single pole/three-way functionality.

Enclosed slider helps prevent dust and dirt contamination.

Exclusive adjustable limit control in incandescent dimmers saves energy and extends lamp life – reduces maximum output by up to 10 percent.

Air gap switch

Improved heat management enables superior load ratings.

Included end caps and spacers screw directly to heat sinks; center plate snaps easily on and off.

Field Uses/Vertical Markets

BOARDROOM

CD703PW

■ Industrial ■ Health Care ■ Education ■ Institutional ■ Retail ■ Office ■ Hospitality/Lodging ■ Multiple Dwelling



Lighting & Fan Controls Titan™ Series Incandescent/Magnetic Low Voltage/Fan

Ordering Information

Catalog Number	Description	Ratings	Narrow or Wide
Incandescent			
CD700*	Single Pole, Slide-to-Off	700W	Narrow
CD1100*		1100W	Narrow
CD 1600*		1600W	Wide
CD2000*		2000W	Wide
CD703-P*	Single Pole/3-Way, Preset	700W	Narrow
CD1103-P*		1100W	Narrow
CD 1603-P*		1600W	Wide
CD2003-P*		2000W	Wide
Magnetic Low Volt	age		
CDLV700-*	Single Pole, Slide-to-Off	700VA	Narrow
CDLV1100-*		1100VA	Narrow
CDLV1600-*		1600VA	Wide
CDLV703-P*	Single Pole/3-Way, Preset	700VA	Narrow
CDLV1103-P*		1100VA	Narrow
CDLV1603-P*		1600VA	Wide
Fan Speed Control			
CDSC6-*	Variable Speed	6A	Narrow
CDSC12-*		12A	Wide
CDDH16-*	Dehummer, 4-Speed	1.6A	Narrow
Adaptor Kit			
CDADAPTORKIT*	Decorator Device Adaptor Kit	_	Narrow



*Color Designation

I Ivory - Brown BK Black
W White GRY Gray LA Light Almond

Notes:

 Replace * with color designation (W-White, I-Ivory, LA-Light Almond, BK-Black, GRY-Gray, Blank-Brown).



Adaptor kit enables matching installation of standard P&S Decorator Devices – outlets, switches, GFCls and more.

CDADAPTORKIT

For more information on these and other P&S products refer to our Catalog or visit our web site.

Lighting & Fan Controls Titan[™] Series Incandescent/Magnetic Low Voltage/Fan



Technical Specifications

3rd Party Compliance

cULus Listed, File Number E95219 Standard UL1472 Solid State Dimming Controls, Standard C22.2 No. 184-1; File Number E109655 Standard UL1917 Solid State Fan Controls, Standard C22.2 No. 156. Conforms to NEMA WD-1 and WD-6. California Title 24 Compliant.

120VAC 60Hz		
Up to rating of device (including derating)		
Thermoplastic enclosure, wall plate, and ganging parts		
Between 0-40°C		
Less than 95% non-condensing		

Materials			
Back Body Front Body Wall Plate End Caps	Thermoplastic Thermoplastic Thermoplastic Thermoplastic	Spacers Heat Sink/Strap Screws	Thermoplastic Aluminum Plated Steel



Warranty


See Instruction Sheet



Dimensions for Narrow Devices

Derating for Multi-Gang Installations

		Fins: NOT Removed		Fins: Removed	
Dimmer Catalog No.	1-Gang Installation	2-Gang Installation	3- or More Gang Installation	2-Gang Installation	3- or More Gang Installation
CD700	700W	700W	700W	700W	700W
CDLV700	700VA	700VA	700VA	700VA	700VA
CD703P	700W	700W	700W	700W	700W
CDLV703P	700VA	700VA	700VA	700VA	700VA
CD1100	1100W	1100W	1000W	1000W	900W
CDLV1100	1100VA	1100VA	1000VA	1000VA	850VA
CD1103P	1100W	1100W	1000W	1000W	950W
CDLV1103P	1100VA	1100VA	1000VA	1000VA	850VA
CD1600	1600W	1600W	1600W	1600W	1550W
CDLV1600	1600VA	1600VA	1600VA	1600VA	1550VA
CD1603P	1600W	1600W	1600W	1600W	1550W
CDLV1603P	1600VA	1600VA	1600VA	1600VA	1550VA
CD2000	2000W	2000W	2000W	n/a	n/a
CD2003P	2000W	2000W	2000W	n/a	n/a



Dimensions for Wide Devices

Refer to installation instructions and sell sheet for the appropriate wall box ganging information

Complementary Devices & Accessories



DECORATOR DEVICES

- Construction Grade Switches
- Specification Grade Combo Switches
- Construction Grade Receptacles
- Commercial Grade Receptacles
- Specification Grade Hallway Lights



GFCIs

- Specification Grade
- Hospital Grade
- PlugTail™

Also available...

- Light Almond Devices
- Hospital Grade Devices
- Switches
- PlugTail™ Devices
- Straight Blade Receptacles
- TVSS & Isolated **Ground Devices**
- Wall Plates
- Straight Blade Plugs & Connectors
- Ground Continuity Monitoring (GCM)
- Turnlok® Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 **Industrial Products**
- Flexcor® Wire Mesh Grips
- Configurable Solutions



Legrand/Pass & Seymour P.O. Box 4822 Syracuse, NY 13221-4822

800-223-4185

North America Headquarters 60 Woodlawn Street West Hartford, CT 06110 Phone: 1.877.BY.LEGRAND (295.3472)

Fax: 1.860.232.2062 www.legrand.us

Legrand Canada 570 Applewood Crescent Vaughan, ON, L4K 4B4 Phone: 905.738.9195 Fax: 905.738.9721

www.legrand.ca