



BURNDY Catalog Number
UPC Number
Description
Status

YGHA272N
7818101692166
CU 3/0, HVY DUTY GRD TER
Active

Web Use
BURNDY Product Line

Dimensional

Thickness 0.29
B Length (in) 1.18
D - in 3.00
Pad Width (in) 1.08
Stud Size (Fraction) 1/2
E - in 1.75

General

Product Description

Copper Compression Lug, Heavy Duty, 2 Hole w/ Inspection Probe Hole, 3/0 AWG, 1/2" Stud, 1-3/4" Stud Hole Spacing, Short Barrel

Conductor(s)

Copper Solid Size (Range) N/A
Copper Stranded (Range) 3/0 AWG

Physical

Type of Plating Unplated
Connector Type Terminal
Plated (Yes or No) N
Index Number 16

Approvals / Certifications

Rated for Direct Burial Y
UL Listed Y
CSA Certified Y
ROHS Compatible Compliant
UL Recognized N
CULUS N
Industry Standards UL468A-468B,UL467,IEEE 837

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175