



BURNDY Catalog Number
UPC Number
Description
Status

BISR3/0DB
 7818102880300
 3/0-1/0 DIRECTBURIALUNIT
 Active

Web Use
 BURNDY Product Line

Screw Size 7/16
 Width (in) 0.99
 Hex Size (Key) 3/16
 Length (in) 6.25
 Height (in) 1.96

Dimensional

Electrical
 600

General

Min Voltage Rating
 Number of Ports 2
 Number of Screws 2
 Product Description In-Line Splice/Reducer, 2 Port, 1/0-3/0 AWG, Al/Cu Rated

Conductor(s)

Aluminum Size (Range) 1/0-3/0 AWG
 Copper Solid Size (Range) N/A
 Copper Stranded (Range) 1/0 -3/0 AWG

Physical

Type of Hardware Aluminum
 Installation Torque 220
 Type of Plating Unplated
 Insulation Type Plastisol
 Plated (Yes or No) N
 Product Material Aluminum

Approvals / Certifications

UL Listed Y
 CSA Certified N
 Rated for Direct Burial Y
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N
 Industry Standards UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175