



Actual

Catalog Number: 33BK
Product ID: 7TBA008900R0014
UPC Number: 06739600768
Status: Active

Black High Temperature Wire Connector, Wire Range #18-#12, Bulk Pack

- External cap made of rugged, phenolic material and 150°C rated.
- Internal round spring design multiplies the twist-on torque applied by the leverage and wedge action, to firmly crush wires into a solid joint.
- Unique copper-coated spring helps resist corrosion.

North American Specifications (UNSPSC)

UNSPSC	39121445 Twist on wire connector
IGCC	4665 Twist on wire connector
Brand Name	Marrette
Type	High Temperature Wire Connectors
Special Features	External cap made of rugged, phenolic material and 150° C rated.
Standard	UL E9809
Material	Thermoplastic Polymer
Color	Black
Voltage Rating	600V
Temperature Rating	302 Degrees F/150 Degrees C

Packaging

Outer Quantity	5000
Outer Dimensions (inches)	15.37x19.75x11.25
Weight Uom	8.13 lbs. per 1000

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
Technical Drawing / Data Sheet Canada	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 860 Ridge Lake Blvd.
 Memphis, TN 38120
www.tnb.com

T&B Technical Support
 MS 3B-50
 860 Ridge Lake Blvd.
 Memphis, TN 38120

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com