


### Pass & Seymour

# Hospital Grade Devices Extra Heavy-Duty Receptacles Tamper-Resistant 15 & 20A, 125V

TR62-H, TR63-H

## Extremely durable receptacles for pediatric locations.

he heavy-gauge brass straps lock into the 100 percent nylon faces and back bodies — ensuring long-term durability. And a sturdy mechanical shutter system helps prevent children from sticking objects into the receptacle. Installation is quick and easy, thanks to screw-pressure-plate back wiring (side wiring is supported too). There is even a back wire clamp on the ground terminal.



#### **Features & Benefits**

**Auto-ground** eliminates the necessity to terminate grounding conductor to device.

**Dual mechanical shutter system** to help prevent insertion of foreign objects.

**Two drive screws anchor strap** to back body and face where abrupt removal torque is strongest.

Exclusive patented feature, circuit label on face of device

allows permanent and positive circuit identification.

Extra heavy-duty brass, one-piece mounting strap with integral ground for

superior structural integrity and long-term performance.


Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.

Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.

One-piece, nickel-plated triple-wipe power contacts for reliable plug retention.



TR63-HI

#### Field Uses/Vertical Markets

Health Care

Education

Institutional



## Hospital Grade Devices **Extra Heavy-Duty Receptacles**Tamper-Resistant 15 & 20A, 125V

#### **Ordering Information**

Catalog Number	Rating A. V.	Color	NEMA Config. No.
Hospital Grade	<b>Duplex Re</b>	<b>ceptacles</b> Back	& Side Wire
TR62-HI	15 125	Ivory	5-15R
TR62-HW	15 125	White	5-15R
TR62-H	15 125	Brown	5-15R
TR62-HGRY	15 125	Gray	5-15R
TR62-HRED	15 125	Red	5-15R
TR62-HLA	15 125	Light Almond	5-15R
TR63-HI	20 125	Ivory	5-20R
TR63-HW	20 125	White	5-20R
TR63-H	20 125	Brown	5-20R
TR63-HGRY	20 125	Gray	5-20R
TR63-HRED	20 125	Red	5-20R
TR63-HLA	20 125	Light Almond	5-20R





## Hospital Grade Devices Extra Heavy-Duty Receptacles Tamper-Resistant 15 & 20A, 125V



#### **Technical Specifications**

#### **3rd Party Compliance**

UL Listed, File Number E140596, Standard UL498. Federal Specification WC596, Hospital Grade. CSA Certified, File Number LR16063, Standard CSA-C22.2 No. 42.

Performance				
Electrical				
Dielectric Voltage	Withstands 2000V minimum			
Maximum Working Voltage	250V			
Current Interrupting	Certified for current interrupting at full-rated current			
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current			
Mechanical				
Terminal Identification	Terminal Identification in accordance with UL498 (Brass, White, Green)			
Terminal Accommodation	#14 AWG - #10 AWG copper conductor only			
Product Identification	Ratings are a permanent part of the device			
Environmental				
Flammability	UL94 V2			
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact			

1.225" Behind Strap .94" –	
1	3.82"
2.80"	0.02
1/0	
11	
060	
1.750"—	


Dimensions for 15 & 20 Amp

Materials	Materials				
Face Back Body Line Contacts	Nylon Nylon 688 Nickel-Plated Brass	Terminal Screws	#10 Tri-Drive Brass (Neutral = Nickel-Plated Steel)		
Mounting Strap Ground Contacts Pressure Plate	.050 688 Brass Strap with Integral Ground .031 260 Nickel-Plated Brass	Ground Screw Assembly Drive Screw Auto-Ground Clip Mounting Screws	#10 Hex Tri-Drive Brass Zinc-Plated Steel Brass Tri-Drive Steel		

#### Warranty

1 Year

#### **Complementary Devices & Accessories**



### HOSPITAL GRADE DEVICES

- Receptacles, Tamper-Resistant, Decorator
- GFCIs
- **■** TVSS
- Isolated Ground
- Plugs & Connectors



#### **PLUGTAIL™ DEVICES**

- Extra Heavy-Duty Hospital Grade Receptacles
- Heavy-Duty Hospital Grade Receptacles
- Extra Heavy-Duty Receptacles




## STRAIGHT BLADE RECEPTACLES

- Extra Heavy-Duty
- Heavy-Duty
- Construction Grade
- Commercial Grade



#### **SWITCHES**

- Heavy-Duty Toggle
- Heavy-Duty Lighted Toggle
- Heavy-Duty Security
- Heavy-Duty Locking
- Construction Grade Toggle
- Commercial Grade Toggle



#### **GFCIs**

- Construction Grade with Auto-Ground
- Construction Grade
- Construction Grade Dead Front



#### WALL PLATES

- TradeMaster® Thermoplastic Nylon
- Stainless Steel
- Brass
- Aluminum
- Dustproof Stainless Steel Covers

#### Also available...

- Light Almond Devices
- Decorator Devices
- TVSS & Isolated Ground Devices
- Ground Continuity Monitoring (GCM)
- Straight Blade Plugs & Connectors
- Turnlok®
   Locking Devices
- Weatherproof Boxes & Covers
- IEC 309 Industrial Products
- Flexcor® Wire Mesh Grips
- Configurable Solutions



**Legrand/Pass & Seymour** P.O. Box 4822

Syracuse, NY 13221-4822 800-223-4185 North America Headquarters 60 Woodlawn Street

West Hartford, CT 06110 Phone: 1.877.BY.LEGRAND (295.3472) Fax: 1.860.232.2062 www.legrand.us Legrand Canada 570 Applewood Crescent Vaughan, ON, L4K 4B4 Phone: 905.738.9195 Fax: 905.738.9721 www.legrand.ca