

DIAMOND DRY CORE BITS

OVERVIEW

MILWAUKEE® Diamond Dry Core Bits are designed to the highest standards, using only quality diamonds. Available in sizes 1"-6", Diamond Dry Core Bits are ideal for drilling brick and block with no reinforcement. The large slots facilitate cooling of the bit as well as extracting the cores. The thinner wall provides increased drilling speed. This bit is 10" in length and contains a 5/8–11 thread.

FEATURES

CUTTING RING

- For use in masonry, brick, and block with no reinforcement
- 10" Drilling Depth
- Designed to be used dry



Size	Thread	Tool Use	Part No.	
1"	5/8"–11	N -	48-17-0010	
1-1/2"	5/8"–11	N -	48-17-0015	
2"	5/8"–11	* -	48-17-0020	
2-1/2"	5/8"–11	N -	48-17-0025	
3"	5/8"–11	× -	48-17-0030	

Size	Thread	Tool Use	Part No.	
3-1/2"	5/8"–11	N -	48-17-0035	
4"	5/8"–11	N -	48-17-0040	
4-1/2"	5/8"–11	N -	48-17-0045	
5"	5/8"–11	×	48-17-0050	
6"	5/8"–11	×	48-17-0060	

DIAMOND CORE BIT ACCESSORIES

DIAMOND CORE BIT ADAPTERS

Description	Thread	Part No.	
5/8"-11 6-Slot Core Bit Adapter	5/8"–11	48-17-6002	
1-1/4"-7 6-Slot Core Bit Adapter	1-1/4"–7	48-17-6004	
Copper Spindle Spacer	-	45-88-8565	
1-1/4" Female - 5/8" Male Core Bit Adapter	1-1/4"–7	48-17-6006	
5/8" Female – 1-1/4" Male Core Bit Adapter	5/8"–11	48-17-6008	

DIAMOND CORE BIT EXTENSIONS

Description	Thread	Part No.	
5/8"-11 x 6" Core Bit Extension	5/8"–11	48-17-6010	
5/8"-11 x 12" Core Bit Extension	5/8"–11	48-17-6012	
1-1/4"-7 x 6" Core Bit Extension	1-1/4"–7	48-17-6014	
1-1/4"-7 x 12" Core Bit Extension	1-1/4"–7	48-17-6016	



OSCILLATING MULTI-TOOL BLADES & ACCESSORIES

OVERVIEW

MILWAUKEE® Oscillating Multi-Tool Accessories provide a complete solution for cutting, scraping, sanding, and grinding across a wide range of materials and applications. Equipped with an OPEN-LOK™ Universal blade anchor for quick blade changes. Made with high quality materials and advanced manufacturing processes to deliver professional grade performance and market leading innovation.

NEW

TITANIUM ENHANCED[™] CARBIDE TEETH BLADES

FEATURES

- TITANIUM ENHANCED[™] Carbide Teeth for up to 50X Longer Life
- Extreme Metal Blade: Cuts through screws, bolts, hard metal, cement board, plaster, and more
- Extreme Materials Blade: Fast cuts through wood with screws, nails, cement board, plaster, copper, and more
- O Universal Fit, OPEN-LOK[™] anchor raised for easy flush cuts and quick blade changes

TITANIUM ENHANCED[™] CARBIDE TEETH BLADES

Description	Materials	1 Pack	2 Pack	3 Pack	5 Pack
1-3/8" TITANIUM ENHANCED" Carbide Teeth Extreme Metal Blade	1 🖓 🏷 🔊	49-25-1501	49-25-1502	49-25-1503	49-25-1505
1-3/8" TITANIUM ENHANCED [™] Carbide Teeth Extreme Materials Blade	🎼 🛹 📲	49-25-1521	49-25-1522	49-25-1523	49-25-1525

DIAMOND CUTTING & CORING OSCILLATING MULTI-TOOL BLADES & ACCESSORIES



