New product

CM-SC Series

Steel pictogram combination unit




Features

- Steel housing with thermoplastic fully adjustable 2W LED heads
- Universal ceiling, side or wall mount
- Universal single and double face
- 3 pictogram panels included: 1 with no arrow and 2 with arrows
- Can power CM-R1 and CM-R2 remote fixtures only
- 120VAC-347VAC, 50/60Hz input
- Lead-acid battery provides minimum 120 minutes of
 emergency lighting
- Red LED charger monitor
- CSA C22.2 no.141-10 listed
- Warranty details at: www.emergi-lite.ca



Dimensions

Dimensions are approximate and subject to change.



Power consumption and unit rating

	AC specs			
Model		Wattage	Current	Efficiency
CM-SC-E	120V, 50/60Hz	3.2W	0.03A	0.97P
	277V, 50/60Hz	6.5W	0.025A	0.92PF
	347V, 50/60Hz	3.6W	0.01A	0.92P

_

Ordering information

Series	Voltage	Brand
CM-SC	Blank= 120VAC-347VAC	-E= Emergi-Lite®
Example: CM-SC-E		

EMERGI-LITE