



CATALOG NO.	"H" BEAM		COPPER CONDUCTOR RANGE				TORQUE Lb -in
			AWG		METRIC WIRE SIZE		
	MIN	MAX	MIN	MAX	MIN	MAX	
GA25G3	1 7/8 X 1 7/8 [48mm X 48mm]	2 1/2 X 2 1/2 [64mm X 64mm]	2/0 sol (.365 DIA.)	250 kcmil(.575 DIA.)	70mm² str [10.9 DIA.]	120mm² str [14.4 DIA.]	240

REV	DATE	DESCRIPTION	ECO	BY	C'H'K.
A	12/14/2017	NEW DRAWING CREATED	48135	PB	RG



- NOTES:**
- MATERIAL: CAST COPPER ALLOY.
 - DIMENSIONS IN BRACKETS [] ARE IN MILLIMETERS ROUNDED OFF TO THE NEAREST MILLIMETER, UNLESS OTHERWISE SPECIFIED AND ARE FOR REFERENCE ONLY.

GROUND CLAMP			
ITEM NO: 26416L			
CAT. NO: GA25G3			
DRAWN BY: B.PARTHIBAN 12/14/2017			
CHECKER: E.MARTIN 1/10/2018			
DSN APRVL: E.MARTIN 1/10/2018			
MFG APRVL: T.WAWRZYNIAK 1/11/2018			
QA APRVL: J.HILLMAN 1/11/2018			
MKT APRVL: --			
PROD FAM: --		DRAWING NO	REV
PROJECT #: --		50088193	A
DOCUMENT TYPE: SALES		SIZE	
REL LEVEL: Released		B	
SHEET 1 OF 1			

TO ORDER BURNDY® PRODUCTS CALL

UNITED STATES
1-800-346-4175 (LONDONDERRY, NH)

CANADA:
1-800-361-6975 (QUEBEC)
1-800-387-6487 (ALL OTHER PROVINCES)

FOR PRODUCT INFO: <http://www.burndy.com>