



KVG-C24288-DWJ

24V Constant Voltage 288W Driver 5-in-1 Dimmable

Project:

Location:

Qty:

Notes:

DESCRIPTION

24V 288W class 2 power supply with built-in wiring compartments for line and low voltage connections




5-in-1 forward and reverse phase dimming:

TRIAC / ELV / MLV, 0-10V, 1-10V, Potentiometer, 10V PWM


FEATURES & BENEFITS

- 120V - 277V AC input
- Built-in power factor correction, PF > 0.98
- Protections:
 - short circuit, over-voltage, over-heat, over-load
- Minimum / Maximum Load: 3 x 9W / 3 x 96W
- Multiple knock-outs for easy wiring
- 0.5 second start time

SPECIFICATION	
Applications	LED Tape, 24V Ceiling Fixtures
Power	3 x 96 W
Input	120V - 277 V AC
Output V / A	24V DC 3 x 4 A
Dimmability	TRIAC, 0-10V, 1-10V, Pot., 10V PWM
Approved Location	Dry, Damp & Wet Locations
Wiring Volume	11 cu in per chamber
Ambient Temperature	-40°F (-40°C) to +140°F (+60°C)
Warranty	5 Year
Certification	c UL us, FCC



Derating Curve - load accordingly



ORDERING GUIDE

KVG-C24288-DWJ

WARNING:

Do not exceed ambient temperature range from -40°F (-40°C) to +140°F (+60°C). Please mount in a shaded area or when mounted indoors install in a well-ventilated area. Failure to follow these instructions could lead to overheating, short life and void the warranty.

COMPLIANCE

Class 2, Type HL, FCC



Lotus LED Lights USA 250 H Street # 301, Blaine WA 98230 tel 360-200-5500 Hainesport NJ, Naples FL, Vancouver WA	www.LotusLEDLights.com mailing addresses warehouses	Lotus LED Lights CANADA 1080 Cliveden Ave # 6, Delta BC V3M 6G6 tel 604-538-3090 Delta BC & Mississauga ON
---	---	---