

PROJECT: _____ DATE: _____

DISTRIBUTOR: _____ CATALOGUE #: _____ TYPE: _____

DRAWN BY: _____ CONTRACTOR: _____ PO: _____



Choice

**SLBW
WEATHERPROOF
BATTERY UNIT**

STANPRO

SPEC SHEET

FEATURES AND SPECIFICATIONS

CIRCUITRY

- LED ultra bright light source
- 120-347 VAC input
- Maintenance free, 7.2V Ni-cad battery
- Wet location
- IP65
- Cold Weather temperature: -25°C to +50°C


MECHANICAL

- High impact thermoplastic construction
- Brownout and short circuit protection
- Test switch and battery charging indicator
- Complete battery recharge in 24 hours
- Universal mounting
- Fully adjustable, LED heads are standard

APPROVALS

- CSA C22.2 #141

TECHNICAL DRAWINGS



A	B	C	D	E
3 1/2" (8.82 cm)	10 1/4" (25.90 cm)	2 3/4" (6.90 cm)	6 5/8" (16.90 cm)	11 1/2" (29.30 cm)

* Please refer to the product web page to view detailed drawings by size.



TECHNICAL SPECIFICATION TABLE

Type	Order Code	Series	Number of Heads	Lamp (W)	Light Source	Input Volts (V AC)	Colour	Option
	70720	SLBW-WH-CW	2	2.5	LED	120-347	White	Cold Weather

SPACING GUIDE

Mounting Height (ft)	Spacing Center to Center (ft)
8	67
10	64
15	58