

PROJECT: _____ DATE: _____

DISTRIBUTOR: _____ CATALOGUE #: _____ TYPE: _____

DRAWN BY: _____ CONTRACTOR: _____ PO: _____



STANPRO

SPEC SHEET

FEATURES AND SPECIFICATIONS


MECHANICAL

- LED ultra bright light source
- 3-12 V DC
- Polycarbonate housing
- Aluminum canopy
- Wet location
- IP65
- Ceiling mount, Wall mount
- Fully adjustable, LED heads are standard
- Operating temperature: -25°C to +50°C

APPROVALS

- cUL

TECHNICAL DRAWINGS



A	B	C	D
6 3/8" (16.19 cm)	5 3/4" (14.61 cm)	9 1/8" (23.18 cm)	4 1/2" (11.43 cm)

* Please refer to the product web page to view detailed drawings by size.



TECHNICAL SPECIFICATION TABLE

Type	Order Code	Series	DC Volts (V DC)	Number of Heads	Lamp (W)	Light Source	Colour
	70681	SWP1	3-12	1	1	LED	White
	70682	SWP2	3-12	2	2	LED	White

SPACING GUIDE

Mounting Height (ft)	Spacing Center to Center (ft)
8	27
10	26
15	20