

PROJECT: _____ DATE: _____

DISTRIBUTOR: _____ CATALOGUE #: _____ TYPE: _____

DRAWN BY: _____ CONTRACTOR: _____ PO: _____



Choice

PRMW
WEATHERPROOF
COMBO RUNNING MAN

STANPRO

SPEC SHEET

FEATURES AND SPECIFICATIONS

CIRCUITRY

- LED ultra bright light source
- 120/347 VAC input
- Maintenance free, 3.6V Ni-MH battery
- Wet location
- IP65
- Cold Weather temperature: -25°C to +50°C


MECHANICAL

- High impact thermoplastic construction
- Universal faces
- Ceiling mount, Wall mount, End mount
- Fully adjustable, LED heads are standard

APPROVALS

- CSA C22.2 #141

TECHNICAL DRAWINGS



A	B	C	D
14" (35.40 cm)	8 7/8" (22.54 cm)	13" (33 cm)	2 1/2" (6.35 cm)

* Please refer to the product web page to view detailed drawings by size.



TECHNICAL SPECIFICATION TABLE

Type	Order Code	Series	Number of Face	Number of Heads	Lamp (W)	Light Source	Input Volts (V AC)	Colour	Option
☐	70678	PRMW0WH-CW	Universal	2	1	LED	120/347	White	Cold Weather

SPACING GUIDE

Mounting Height (ft)	Spacing Center to Center (ft)
8	32
10	31
15	25



Comes standard with three pictogram legends for direction selection.

INCLUDED IN THE BOX