

F40T12/NX/ALTO 30PK

927888004904



Superior color rendering

Philips T12 High CRI Lamps are energy-efficient lighting solutions and provide excellent color consistency over the life of the lamp.

General Information

Cap-Base	G13 [Medium Bi-Pin Fluorescent]
Features	ALTO® (ALTO)

Light Technical

Luminous Flux	2,550 lm
Color Designation	Neutral DX
Correlated Color Temperature (Nom)	3500 K
Color rendering index (CRI)	88

Operating and Electrical

Power Consumption	40 W
-------------------	------

Mechanical and Housing

Bulb Shape	T-12
Net Weight (Piece)	0.230 kg

Approval and Application

Energy Saving Product	Energy Saving
Mercury (Hg) Content (Nom)	4.4 mg

Product Data

Order product name	F40T12/NX/ALTO 30PK
Full product name	F40T12/NX/ALTO 30PK
Order code	927888004904
Material Nr. (12NC)	927888004904
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677423186
Numerator - Packs per outer box	30
EAN/UPC - Case	50046677423181

Dimensional drawing

Product

F40T12/NX/ALTO 30PK

