

PHILIPS

**14A19/CNG/827/FR/P/E2
6/ND 4/1CT**

929002311764



Contractor grade, LEDbulb, A19, not dimmable, 100 W, E26, 2700 K, 1500 lm, 15000 hour(s), Plastic

Contractor grade, LEDbulb, A19, not dimmable, 100 W, E26, 2700 K, 1500 lm, 15000 hour(s), Plastic, 107 lm/W

General Information

Cap-Base	E26
Nominal lifetime	15,000 hour(s)
Switching Cycle	50,000
Lighting Technology	LEDbulb

Light Technical

Color Code	827 [CCT of 2700K]
Beam Angle (Nom)	150 degree(s)
Luminous Flux	1,500 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	107 lm/W

Color Consistency	<6
Color rendering index (CRI)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %

Operating and Electrical

Input Frequency	60 Hz
Power Consumption	14 W
Lamp Current (Nom)	255 mA
Wattage Equivalent	100 W
Starting Time (Nom)	0.5 s
Warm-up time to 60% light	0.5 s
Power Factor (Fraction)	0.5
Voltage (Nom)	120 V

Temperature

T-Case Maximum (Nom)	95 °C
----------------------	-------

Controls and Dimming

Dimmable	No
----------	----

Mechanical and Housing

Bulb Finish	Frosted
Bulb Material	Plastic
Bulb Shape	A19
UL Wet/ damp/ dry location	Damp location
Net Weight (Piece)	0.036 kg

Approval and Application

EU RoHS compliant	Yes
T20 compliant	No
Ambient temperature range	-20 to +45 °C


Application Conditions

can it be used in closed luminaires	No
Wireless Technology	Not applicable

Product Data



Order product name	14A19/CNG/827/FR/P/E26/ND 4/1CT
Full product name	14A19/CNG/827/FR/P/E26/ND 4/1CT
Order code	929002311764
Material Nr. (12NC)	929002311764
Numerator - Quantity Per Pack	1
EAN/UPC - Product/Case	046677588953
Numerator - Packs per outer box	4
EAN/UPC - Case	50046677588958

Dimensional drawing



Product	D	C
14A19/CNG/827/FR/P/E26/ND 4/1CT	60 mm	117 mm


Photometric data




Spectral Power Distribution Colour -
14A19/CNG/827/FR/P/E26/ND 4/1CT

General uniform lighting - 14A19/CNG/827/FR/P/E26/ND 4/1CT

Lifetime



Life Expectancy Diagram



Lumen Maintenance Diagram - 14A19/CNG/827/FR/P/E26/ND 4/1CT

Related Documents

Documents and certificates	Document Name	Download
Environmental Product Declaration	EPD-Phi-Contractor-grade-Plastic-Non-Dimmable-A-Shape-Lamps-FAM-10428701-Ref-929002311764-EPD.pdf	Download 
Photometry and lighting design	Document Name	Download
IES File	LEDbulb_14W_E26_A9_827_FR-IES.IES	Download 

