

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT PART #	STUD SIZE		DIMENSIONS in. [mm]				
	AWG	METRIC	L ± .03 [0,8]	W ± .01 [0,3]	C ± .02 [0,5]	M ± .03 [0,8]	H ± .01 [0,3]
PNF18-4R	#4	--	.77 [19,6]	.25 [6,4]	.20 [5,1]	.65 [16,5]	.12 [3,0]
PMNF1-3R	--	M3	.76 [19,3]	.23 [5,8]	.21 [5,3]	.66 [16,8]	.13 [3,3]
PNF18-6R	#6	M3,5	.77 [19,6]	.25 [6,4]	.20 [5,1]	.65 [16,5]	.15 [3,8]
PNF18-6RN	#6	M3,5	.76 [19,3]	.22 [5,6]	.18 [4,6]	.63 [16,0]	.15 [3,8]
PNF18-8R	#8	M4	.87 [22,1]	.31 [7,9]	.24 [6,1]	.72 [18,3]	.17 [4,3]
PNF18-10R	#10	--	.87 [22,1]	.31 [7,9]	.25 [6,4]	.72 [18,3]	.20 [5,1]
PMNF1-5R	--	M5	.86 [21,8]	.35 [8,9]	.25 [6,4]	.69 [17,5]	.21 [5,3]
PNF18-14R	1/4"	M6	1.08 [27,4]	.46 [11,7]	.38 [9,7]	.85 [21,6]	.27 [6,9]

UL & CSA TOOLS (DIES)

CT-100A
CT-220C
CT-250
CT-400
CT-500CH
CT-600-A (CT-500CH)
CT-600-A (CT-550CH)
CT-1550
CT-1551
CT-2300
CT-2400 (CT-2400CH /CHA)
CT-2500 (CT-2550CH)

PANDUIT APPROVED TOOLS

CT-160
CT-260



.136 [3,45]
MAX. WIRE
INSUL. DIA.

.070 [1,78]
MIN. WIRE
INSUL. DIA.



LISTED
587H
E52164



CERTIFIED
LR31212

NOTES:

- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- DIMENSIONS IN [] ARE METRIC.
- WEIGHT: .002 TO .004 Lbs. APROX.
- PART INCLUDES:
 - STAMPING: .03" [0,8mm] THK COPPER, TIN PLATED
 - HOUSING: NYLON, RED
 - SLEEVE: BRASS, TIN PLATED
- UL LISTED AND CSA CERTIFIED FOR:
 - #22-18 AWG [0,5-1,0 mm²] SOLID OR STRANDED COPPER WIRE
 - 221°F [105°C] MAX. OPERATING TEMPERATURE.
 - 600 V. MAX. VOLTAGE RATING, 1000 V. IN SIGNS, FIXTURES & LUMINARIES

- WIRE STRIP LENGTH: 7/32" ^{+1/32}₋₀ [5,6mm ^{+0,8}₋₀]

15	12-05-25	ANVM	ANVM	JSUN	UPDATED PNF18-10R "W" DIMENSION FROM 0.32 TO 0.31	028255/00
14	10-22-25	DPOI	DPOI	JSUN	REMOVED MILITARY SPEC CLASS 2 IN CHART & TOOLS. REMOVED OBSOLETE PNS: PNF18-4RN & PNF18-56R & USE UP PN: PNF18-38R. ADDED NEW TOOLS: CT-220C/250/400/500CH/2300/2400	022463/00
13	01-01-25	TMR	TMR	RGB	AGENCY CERTIFICATION AND TABLE FORMA UPDTAED.	N1275BA-A41275
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

PART NUMBER		SEE TABLE	
TITLE		RING TERMINALS, 3 PC. NYLON INSULATED, #22-18 AWG, FUNNEL ENTRY (PNF18)	
ITEM REVISION NAME		CUSTOMER DRAWING	
DATASET FILE NAME		N41275BA/15	
MATERIAL		N41275BA_DC r15A	
DRAWN BY		DAW	
DATE		-	
CHK		LM	
SCALE		N.T.S.	
DRAWING NUMBER		A41275	
SHEET 1 OF 1		A	