


# RT-MINI II

A Self-flashing PV Mount Featuring Roof Tech's AlphaSeal®



RT-MINI II is suitable for any conventional L-Foot

- **ALPHA SEAL™ Self-Flashing System**
- **No Caulking or Pre-Drilling Required**
- **Universal Attachment to Steep & Low Slope**
- **UL 2703 A Certified**
- **Metal, EPDM, TPO, SBS, & Asphalt**
- **North-South & Rotational Adjustments**
- **Perfect L-foot/rail connection due to adjustability**



**RT L-Foot Bracket**  
Comes in Black Coated or Mill Finish.

Manual




**Roof Tech**

[www.roof-tech.us](http://www.roof-tech.us) [info@roof-tech.us](mailto:info@roof-tech.us)



# RT-MINI II


Flexible Flashing Certified by the International Code Council (ICC)



PLYWOOD OR OSB ONLY

## Components

RT2-00-MINIBK2-FSET



MINI II base : 20 ea.  
Screw : 40 ea.  
Bolt & Nut Set: 20 ea.  
Extra RT-Butyl : 4 ea.

### Optional Items:

5 x 60mm Mounting Screw (RT2-04-SD5-60) : 100 ea./Bag  
5 x 90mm Mounting Screw (RT2-04-SD5-90) : 100 ea./Bag


RT L-Foot: 20 ea.

RT2-04-LFT4476 - Mill - 0 L-Foot Slotted 3/8"

RT2-04-LFT4476 - BLK - 0 L-Foot Slotted 3/8"

RT-Butyl(RT2-04-MNBUTYL) :10 ea./Box

## Dimensions in (mm)



Roof Tech's AlphaSeal System has been used on over one million residential PV systems since 1994. It is the first PV mounting system with Flexible Flashing certified by the ICC, engineered to withstand wind speeds up to 190 mph and ground snow up to 120 psf.



Engineered to ASTM D 1761  
Flexible Flashing ICC ESR-3575  
UL 2703A, UL 441 (27), TAS  
100(A)-95, ASTM E 2140



Support & Downloads

**Roof Tech**

www.roof-tech.us

10620 Trenea Street, Suite 230, San Diego, CA 92131

858.935.6064