



IP710-D0Z

IllumaTech Dimmer Switch for 0-10V LED, Mark 7 Fluorescent Ballasts

IllumaTech Slide Preset Electro-Mechanical 0-10V Slide Dimmer for use with LED or Fluorescent Ballasts and Power Supplies, suitable for use with Class 1 or Class 2 wiring, 1200VA @ 120VAC, 1500VA @ 277VAC, 10A LED/Electronic Ballast 120 /277VAC, 60Hz, 50mAmps maximum sinking current, single pole or 3-way control when used with 3-way switch - White, Ivory & Light Almond

UPC Code : 078477943557

Country Of Origin : Please Contact Customer Service

- INNOVATIVE – Designed for use with LED fixtures using 0-10V power supplies for dimming lighting in commercial spaces such as hotels, restaurants, offices and other public spaces
- ADVANCED – No power pack required for switching
- EXCEPTIONAL – Superior quality and dimming performance
- CONVENIENT – Separate on/off switch allows you to set and keep preferred dimming level
- STYLISH – Easily change the color using IPKIT-LN faceplates available in white, ivory, light almond, gray, black, brown and red

Technical Information

Product Features

Action : Standard ON/OFF

Available Colors : Ivory, White, Gray, Black, Brown, Light Almond, and Red

Color : White, Ivory, Light Almond

Device Type : Dimmer

Frequency : 60Hz

Load Rating : 10A, 1200VA, 1500VA

Load Type : Electronic 0-10VDC Fluorescent and 0-10VDC LED Power Supply

Ordering Notes : White, Ivory, Light Almond Color Kits

Preset : Preset

Protection : Radio/TV Filter

Standards and Certifications : cCSAus

Style Name : Illumatech

Switch Type : Single-Pole & 3-Way

Type : Slide

Voltage : 120/277 VAC

Wallplate : Order Separately

Warranty : 5-Year Limited

Features and Benefits

- Designed specifically for use with LED fixtures using 0-10V power supplies and Mark 7® 0-10V fluorescent ballasts
- Dual voltage 120V/277V; 50mAmps maximum sink current
- No power pack required for switching
- Provides single pole or 3-way lighting control when used with a 3-way switch
- Compatible with Decora Plus™ screwless and Decora standard designer wallplates (sold separately)
- Change the color using IPKIT-LN faceplates available in white, ivory, light almond, gray, black, brown and red
- Fluid slide movement allows fine adjustment of light level with minimal effort
- Captive wraparound slide bar remains securely attached

Patents*

N_A

This list is provided for patent marking purposes only. A good faith effort is made to maintain the accuracy and completeness of this list. No legal inference should be drawn from the omission of a patent from this list.

SPECIFICATION SUBMITTAL

JOB NAME: 	CATALOG NUMBERS: 	
JOB NUMBER: 		

Leviton Manufacturing Co., Inc

201 North Service Road, Melville, NY 11747

Telephone: +1-800-323-8920 · FAX: +1-800-832-9538 · Tech Line (8:30AM-7:30PM E.S.

T. Monday-Friday): +1-800-824-3005

Leviton Manufacturing of Canada, Ltd.

165 Hymus Boulevard, Pointe Claire, Quebec H9R 1E9 · Telephone: +1-800-461-2002 ·

FAX: +1-800-824-3005 ·

Leviton S. de R.L. de C.V.

Lago Tana 43, Mexico DF, Mexico CP 11290 · Tel.: (+52)55-5082-1040 · FAX: (+52)

5386- 1797 ·

Visit our Website at: www.leviton.com

© 2026 Leviton Manufacturing Co., Inc. All Rights Reserved. Subject to change without notice.

Leviton has a global presence.

If you would like to know where your local Leviton office is located please go to:

www.leviton.com/company/about-leviton/locations

