

VTL24-CCT

Vapor tight linear strip light



NAME:	
TYPE:	
DATE:	
NOTES:	

SPECIFICATIONS

WIRING:	Hardwire only. The knockout on the end of the fixture comes standard with a watertight KO connector. Always use watertight KO connector to ensure a tight seal.
HOUSING DETAILS:	The vapor tight housing is made of durable PVC and the lens has an IPK10 rating. All lens mounting clips are stainless steel to avoid corrosion and the silicone gasket seal provides a full wet location rating (IP67). Easily surface or suspended mounted using the spring steel mounting clips that snap on to the back of the housing.
OPTICS:	Offered with an acrylic frosted diffuser lens and LED technology to distribute light and optimize delivered high level of lumens.
ELECTRICAL:	Easily connected to a 120-347V power supply via provided UL recognized wide range voltage driver. 0-10V dimmable WET LOCATIONS rated – IP67 Certifications: This product is cETLus, DLC 5.1 Premium listed and has NSF rating for use in the food processing industry in USA and Canada. Ambient operating temperature -40°F (-40°C) to 104°F (+40°C) NEMA 4X - Corrosion resistant materials
LENS:	The MAMBA Series has a frosted diffuser providing a uniform and widespread illumination.


COLOR TEMPERATURE:	35K - 4K - 5K selectable
LUMEN OUTPUT:	2250 / 2600 / 3000 lumens
DIMMABLE:	Yes
WATTS:	14W / 17W / 20W selectable
LED LIFE:	50,000 hours
WARRANTY:	5 years
VOLTAGE:	120-347V
EFFICACY:	150lm/W
HEIGHT:	3.4" (8.6 cm)
LENGTH:	26.1" (66.3 cm)
WIDTH:	4" (10.2 cm)
INTEGRATED MOTION SENSOR:	No

APPLICATIONS

The vapor tight linear light is ideal for many indoor and outdoor applications including stairwells, warehousing, marinas, multi-level parking lots, barns and other agricultural uses and many more.

VTL24-CCT
Vapor tight linear strip light

DIMENSIONS



RATINGS



ORDERING GUIDE

MAMBA VAPOR TIGHT LINEAR SERIES

Series	Selectable Color Temperature	Finish
VTL24	CCT 3500K-4000K-5000K	GR Grey
Notes:	Configure product using BOLD options: Ex: VLT24-CCT-GR	