



ONE-DOOR UNIVERSAL FREE-STAND ENCLOSURES, TYPE 4

Catalog Number	A×B×C in./mm	Sides Open	Cutout Type	Material	Panel, Painted	Panel, Conductive	Panel Size in./mm
AU72X4018BLP	72.13 × 39.76 × 18.11 1832 × 1010 × 460	Both	No Cutout	Mild Steel	A72PM40	A72PM40G	60.00 × 33.75 1524 × 857
AU72X4018LLP	72.13 × 40.24 × 18.11 1832 × 1022 × 460	Left	Preferred	Mild Steel	A72PM40	A72PM40G	60.00 × 33.75 1524 × 857
AU72X4018LUCLP	72.13 × 40.24 × 18.11 1832 × 1022 × 460	Left	Universal	Mild Steel	A72PM40	A72PM40G	60.00 × 33.75 1524 × 857
AU72X4018RLP	72.13 × 39.76 × 18.11 1832 × 1010 × 460	Right	No Cutout	Mild Steel	A72PM40	A72PM40G	60.00 × 33.75 1524 × 857
AU84X4018BLP	84.13 × 39.76 × 18.11 2137 × 1010 × 460	Both	No Cutout	Mild Steel	A84PM40	A84PM40G	72.00 × 33.75 1829 × 857
AU84X4018LLP	84.13 × 40.24 × 18.11 2137 × 1022 × 460	Left	Preferred	Mild Steel	A84PM40	A84PM40G	72.00 × 33.75 1829 × 857
AU84X4018LUCLP	84.13 × 40.24 × 18.11 2137 × 1022 × 460	Left	Universal	Mild Steel	A84PM40	A84PM40G	72.00 × 33.75 1829 × 857
AU84X4018RLP	84.13 × 39.76 × 18.11 2137 × 1010 × 460	Right	No Cutout	Mild Steel	A84PM40	A84PM40G	72.00 × 33.75 1829 × 857
AU84X4024BLP	84.13 × 39.76 × 24.13 2137 × 1010 × 613	Both	No Cutout	Mild Steel	A84PM40	A84PM40G	72.00 × 33.75 1829 × 857
AU84X4024LLP	84.13 × 40.24 × 24.13 2137 × 1022 × 613	Left	Preferred	Mild Steel	A84PM40	A84PM40G	72.00 × 33.75 1829 × 857
AU84X4024LUCLP	84.13 × 40.24 × 24.13 2137 × 1022 × 613	Left	Universal	Mild Steel	A84PM40	A84PM40G	72.00 × 33.75 1829 × 857
AU84X4024RLP	84.13 × 39.76 × 24.13 2137 × 1010 × 613	Right	No Cutout	Mild Steel	A84PM40	A84PM40G	72.00 × 33.75 1829 × 857
AU90X4018BLP	90.13 × 39.76 × 18.11 2286 × 1010 × 460	Both	None	Mild Steel	A90PM40	A90PM40G	78.00 × 33.75 1982 × 857
AU90X4018LLP	90.13 × 39.76 × 18.11 2286 × 1010 × 460	Left	Preferred	Mild Steel	A90PM40	A90PM40G	78.00 × 33.75 1982 × 857
AU90X4018LUCLP	90.13 × 39.76 × 18.11 2286 × 1010 × 460	Left	Universal	Mild Steel	A90PM40	A90PM40G	78.00 × 33.75 1982 × 857
AU90X4018RLP	90.13 × 39.76 × 18.11 2286 × 1010 × 460	Right	None	Mild Steel	A90PM40	A90PM40G	78.00 × 33.75 1982 × 857
AU90X4024BLP	90.13 × 39.76 × 24.13 2286 × 1010 × 613	Both	None	Mild Steel	A90PM40	A90PM40G	78.00 × 33.75 1982 × 857
AU90X4024LLP	90.13 × 39.76 × 24.13 2286 × 1010 × 613	Left	Preferred	Mild Steel	A90PM40	A90PM40G	78.00 × 33.75 1982 × 857
AU90X4024LUCLP	90.13 × 39.76 × 24.13 2286 × 1010 × 613	Left	Universal	Mild Steel	A90PM40	A90PM40G	78.00 × 33.75 1982 × 857
AU90X4024RLP	90.13 × 39.76 × 24.13 2286 × 1010 × 613	Right	None	Mild Steel	A90PM40	A90PM40G	78.00 × 33.75 1982 × 857



TWO-DOOR UNIVERSAL FREE-STAND ENCLOSURES, TYPE 4

Catalog Number	A×B×C in./mm	Sides Open	Cutout Type	Material	Panel, Painted	Panel, Conductive	Panel Size in./mm
AU72X7818BLP	72.13 × 77.99 × 18.11 1832 × 1981 × 460	Both	No Cutout	Mild Steel	A72PM78	A72PM78G	60.00 × 72.00 1524 × 1829
AU72X7818LLP	72.13 × 78.50 × 18.11 1832 × 1994 × 460	Left	Preferred	Mild Steel	A72PM78	A72PM78G	60.00 × 72.00 1524 × 1829
AU72X7818LUCLP	72.13 × 78.50 × 18.11 1832 × 1994 × 460	Left	Universal	Mild Steel	A72PM78	A72PM78G	60.00 × 72.00 1524 × 1829
AU72X7818RLP	72.13 × 77.99 × 18.11 1832 × 1981 × 460	Right	No Cutout	Mild Steel	A72PM78	A72PM78G	60.00 × 72.00 1524 × 1829
AU84X7818BLP	84.13 × 77.99 × 18.11 2137 × 1981 × 460	Both	No Cutout	Mild Steel	A84PM78	A84PM78G	72.00 × 72.00 1829 × 1829
AU84X7818LLP	84.13 × 78.50 × 18.11 2137 × 1994 × 460	Left	Preferred	Mild Steel	A84PM78	A84PM78G	72.00 × 72.00 1829 × 1829
AU84X7818LUCLP	84.13 × 78.50 × 18.11 2137 × 1994 × 460	Left	Universal	Mild Steel	A84PM78	A84PM78G	72.00 × 72.00 1829 × 1829
AU84X7818RLP	84.13 × 77.99 × 18.11 2137 × 1981 × 460	Right	No Cutout	Mild Steel	A84PM78	A84PM78G	72.00 × 72.00 1829 × 1829
AU84X7824BLP	84.13 × 77.99 × 24.13 2137 × 1981 × 613	Both	No Cutout	Mild Steel	A84PM78	A84PM78G	72.00 × 72.00 1829 × 1829
AU84X7824LLP	84.13 × 78.50 × 24.13 2137 × 1994 × 613	Left	Preferred	Mild Steel	A84PM78	A84PM78G	72.00 × 72.00 1829 × 1829
AU84X7824LUCLP	84.13 × 78.50 × 24.13 2137 × 1994 × 613	Left	Universal	Mild Steel	A84PM78	A84PM78G	72.00 × 72.00 1829 × 1829
AU84X7824RLP	84.13 × 77.99 × 24.13 2137 × 1981 × 613	Right	No Cutout	Mild Steel	A84PM78	A84PM78G	72.00 × 72.00 1829 × 1829
AU90X7818BLP	90.13 × 77.99 × 18.11 2286 × 1981 × 460	Both	None	Mild Steel	A90PM78	A90PM78G	78.00 × 72.00 1982 × 1829
AU90X7818LLP	90.13 × 77.99 × 18.11 2286 × 1981 × 460	Left	Preferred	Mild Steel	A90PM78	A90PM78G	78.00 × 72.00 1982 × 1829
AU90X7818LUCLP	90.13 × 77.99 × 18.11 2286 × 1981 × 460	Left	Universal	Mild Steel	A90PM78	A90PM78G	78.00 × 72.00 1982 × 1829
AU90X7818RLP	90.13 × 77.99 × 18.11 2286 × 1981 × 460	Right	None	Mild Steel	A90PM78	A90PM78G	78.00 × 72.00 1982 × 1829
AU90X7824BLP	90.13 × 77.99 × 24.13 2286 × 1981 × 613	Both	None	Mild Steel	A90PM78	A90PM78G	78.00 × 72.00 1982 × 1829
AU90X7824LLP	90.13 × 77.99 × 24.13 2286 × 1981 × 613	Left	Preferred	Mild Steel	A90PM78	A90PM78G	78.00 × 72.00 1982 × 1829
AU90X7824LUCLP	90.13 × 77.99 × 24.13 2286 × 1981 × 613	Left	Universal	Mild Steel	A90PM78	A90PM78G	78.00 × 72.00 1982 × 1829
AU90X7824RLP	90.13 × 77.99 × 24.13 2286 × 1981 × 613	Right	None	Mild Steel	A90PM78	A90PM78G	78.00 × 72.00 1982 × 1829