




ROTATABLE COB LED CORDLESS WORK LIGHT- 5,000LM

- **Worksite Applications:** Suitable for worksites, garages, outdoor tasks, and emergency lighting.
- **Multi-Brand Battery Compatibility:** Works with most third-party 18V-20V batteries including DeWalt®, Milwaukee®, Makita®, Bosch®, Metabo HPT®, and RIDGID® (adapters included). No sponsorship or affiliation with third party brands suggested or implied.
- **Adjustable Light Panels:** Center panel rotates 180°. Side panels adjust 360° vertically and 180° horizontally for directional lighting coverage.
- **Tripod Mount Compatible:** Threaded base allows secure mounting on a tripod stand (tripod not included).


L002922

 1/12
CASE


LED CORDLESS WORK LIGHT - 3,000 LM

- **Worksite Applications:** Suitable for worksites, garages, outdoor tasks, emergencies, and roadside assistance.
- **Multi-Brand Battery Compatibility:** Works with most third-party 18V-20V batteries including DeWalt®, Milwaukee®, Makita®, Bosch®, Metabo HPT®, and RIDGID® (adapters included). No sponsorship or affiliation with third party brands suggested or implied.
- **3 Brightness Levels:** High, Medium, and Low settings deliver up to 3000 lumens with 6000K daylight color temperature for clear illumination.
- **Lightweight Durable Housing:** ABS construction designed for portability and everyday jobsite use.
- **USB Output Port:** Built-in 5V / 1A USB port allows charging of phones and small devices.

L002920

 1/12
CASE




Designed for worksites, workshops, garages, and emergency situations, portable LED work lights provide bright, adjustable illumination wherever you need it. With dual power options, long-lasting battery life, and built-in USB charging, these lights offer unmatched convenience for both professional and personal use. Featuring rugged, weather-resistant construction, versatile mounting options, and customizable brightness levels, they deliver efficient, high-performance lighting for any job.

HYBRID LED TRIPOD WORK LIGHT - 10,000LM

- Perfect for construction sites, workshops, warehouses, industrial job sites, outdoor events, and emergency lighting
- **6-Light Modes:** Easily adjust between six brightness levels, delivering up to a max 10,000 lumens on AC power or 5,000 lumens max on battery.
- **Ultra-Bright & Wide-Area Coverage:** Delivers 10,000 lumens with two rotatable light heads, illuminating up to 2,150 sq. ft. (200m²) with 5500/6500K daylight brightness.
- **Dual Power Flexibility:** Runs on 120V AC mains power (100-240V, 50-60Hz, 90W) or a 16V 5200mAh rechargeable Lithium battery (40W).
- **Rechargeable & Long-Lasting:** Up to 2 hours of runtime on battery power and fully recharges in 3 hours for quick turnaround.
- **Compact & Adjustable:** Collapsible design folds to 35" x 7.5" x 4.5" and extends up to 7.5 feet for optimal lighting.
- **USB Power Output:** Features USB-A and USB-C output ports, allowing you to charge other portable devices directly from the light.
- 1.5m 16AWG cord, Type-C cable and Carrying bag included.

L002916 1/1
CASE

