

INTERIOR HOUSEHOLD EXTENSION

Power Tap Extension Cords 3-Outlet

- solid molded power taps • 3-outlet compact design • grounded • 3-conductor molded plug • wire gauge: 16-3 • wire type: SPT-3 • rated: 13A/125V • CSA approved • white color • for video equipment, computers & office machines



Item #	UPC	Description	Pack
WD-537850	062964378502	2M WHITE 16/3	1/20
WD-542652	062964426524	3M WHITE 16/3	1/18
WD-542654	062964426548	4.5M WHITE 16/3	1/28

AIR CONDITIONER CORDS

Medium Duty Air Conditioner Cord

- solid molded single outlet • 3-conductor grounded right angle male plug • wire gauge: 16-3 • wire type: SPT-3 • rated: 13A/125V • CSA approved • beige cord • for air conditioner, freezer, refrigerator, power tools & other major appliances



Item #	UPC	Description	Pack
WD-537802	062964378021	2M BEIGE 16/3	1/36
WD-542615	062964426159	3M BEIGE 16/3 (REPL. WD-10832)	1/28
WD-542648	062964426487	4.5M BEIGE 16/3 (REPL. WD-10833)	1/20

SLIMLINE™ Household Extension Cord 3-Outlet

- special designed male plug keeps cord close to the wall • wire gauge: 16-2 • wire type: SPT-2 • rated: 13A/125V • CSA approved • white cord • perfect for behind furniture (sofa, table, nightstand, etc.), behind appliances in kitchen or office, electric wall clocks, behind TV & audio system cabinets • 3-outlet female end



Item #	UPC	Description	Pack
WD-540499	062964404997	2.5M WHITE 16/2	1/24
WD-540504	062964405048	4M WHITE 16/2	1/20

Heavy Duty Air Conditioner Cord

- solid molded single outlet • 3-conductor grounded right angle male plug • wire gauge: 14-3 • wire type: SPT-3 • rated: 13A/125V • CSA approved • grey cord • for air conditioner, freezer, refrigerator, power tools & other major appliances



Item #	UPC	Description	Pack
WD-542660	062964426609	2M GREY 14/3 (REPL. WD-10044)	1/36
WD-542673	062964426739	3M GREY 14/3 (REPL. WD-10045)	1/28
WD-542699	062964426999	4.5M GREY 14/3 (REPL. WD-10047)	1/20

Indoor Dual Cord

- convenience of 2 cords built into cord set • low profile plug design allows furniture to be safely placed against the wall • two 3.6M extensions each with 3-outlets polarized • to run appliances or lights on either side of furniture or beds • each outlet has a safety slide cover when not used • white



Item #	UPC	Description	Pack
WD-540150	062964401507	DUAL CORD WHITE	1/8

INDOOR CORDS

Office Equipment Cords 3-Outlet

- great for computers and most office equipment • low profile right angle molded plug • allows cord to lay flat against the wall for safety and neatness • solid molded 3-outlet power tap female end • hanging loop for convenience and ease of use • grey color • new 2006 • 14/3 SPT-3 wire type



Item #	UPC	Description	Pack
WD-537901	062964379011	2M GREY 14/3	1/36
WD-542703	062964427033	3M GREY 14/3	1/28
WD-542705	062964427057	4.5M GREY 14/3	1/20

CHRISTMAS/PATIO CORDS

Christmas/Patio Indoor/Outdoor Cord

- 3 polarized outlets • 2-conductor solid molded plug • comes with safety receptical cap • wire gauge: 16-2 • wire type: PXWT • rated: 13A/125V
- CSA approved • available in green or white cord
- for indoor/outdoor temporary use



Item #	UPC	Description	Pack
WD-542709	062964427095	3M GREEN 16/2	1/25
WD-542710	062964427101	3M WHITE 16/2	1/25
WD-542711	062964427118	4.5M WHITE 16/2	1/20
WD-542725	062964427255	4.5M GREEN 16/2	1/20

9-Outlet Christmas Specialty Indoor Cords

- total length 111" (9'3") • 3x3 outlet plugs spaced 21" apart on 1-cord are polarized with safety slide covers if not in use • inline on/off switch is 19" from last outlet and 31" from plug in • use up to 10 strings of indoor mini (push in) lites or maximum 625-watts of screw in lights • replaceable 5-amp safety fuse • green for Christmas trees or white for Christmas "village" displays



Item #	UPC	Description	Pack
WD-40276	062964402764	GREEN TREE CORD	1/15
WD-40277	062964402771	WHITE VILLAGE	1/15

Easy Switch Indoor Extension Cord

- easy access on/off switch on 16 gauge 16-2 white or green cord • SPT-2 10-Amp cord • remote operation of Christmas lights, lamps, appliances • display box



Item #	UPC	Description	Pack
WD-548250	062964482582	3.0M WHITE 16/2	1/12
WD-548261	062964482612	3.0M GREEN 16/2	1/12

Foot Switch Light Controller Indoor Use

- easy access convenient on/off switch • white or green cord • 16-2 SPT-2 wire • 13-Amp • cord is rated for 1625 watts (normally 3000 mini lites or 200 C-7 lites) • 3-outlet • polarized plug and outlet



Item #	UPC	Description	Pack
WD-548290	062964482902	3M WHITE 16/2	1/8

OUTDOOR CORDS

Outdoor Cord 1-Outlet/3-Conductor

- heavy duty • copper conductors • solid molded plug • single outlet • 2 layers of insulation • resists deterioration from moisture & abrasion • 300V • non-marking coating • wire gauge: 14-3 • wire type: SJTW • CSA approved • red cord



Item #	UPC	Description	Pack
WD-541570	062964415702	8M RED 14/3	1/13
WD-541574	062964415740	15M RED 14/3	1/8
WD-536778	062964367780	30M RED 14/3	1/3

Power Tool Outdoor Cords 1-Outlet

- medium duty • copper conductors • single outlet • 2 layers of insulation • resists deterioration from moisture & abrasion • 300V • non-marking coating • wire gauge: 16-3 • wire type: SJTW • CSA approved • orange cord



Item #	UPC	Description	Pack
WD-541504	062964415047	3M ORANGE 16/3	1/14
WD-541506	062964415061	5M ORANGE 16/3	1/21
WD-541522	062964415221	10M ORANGE 16/3	1/12
WD-541548	062964415481	15M ORANGE 16/3	1/10
WD-541564	062964415641	30M ORANGE 16/3	1/3

Outdoor Cord 3-Outlet/ 3-Conductor

- medium duty • copper conductors • solid molded plug • 3 outlets • 2 layers of insulation • resists deterioration from moisture & abrasion • 300V • non-marking coating • wire gauge: 16-3 • wire type: SJTW • CSA approved • orange cord

IIIWoods®



Item #	UPC	Description	Pack
WD-540650	062964456507	3M ORANGE 16/3	1/14
WD-545454	062964454541	5M ORANGE 16/3	1/21
WD-545502	062964455029	10M ORANGE 16/3	1/12
WD-545528	062964455289	15M ORANGE 16/3	1/10

Green Cube Tap Heavy Duty 3-Outlet

- molded solid cube body • 3 outlets grounded • green color • exterior • CSA approved

IIIWoods®



Item #	UPC	Description	Pack
WD-580794	062964507940	GREEN 3-WAY	1/25

Outdoor Cord 1-Outlet Indicator Light

- medium duty cord with copper conductors • double insulated cover • waterproof UV resistant • flexible in extreme cold • POWERLITETM glows when cord has power • SJTW type wire

IIIWoods®



Item #	UPC	Description	Pack
WD-541508	062964415085	5M ORANGE 16/3	1/21
WD-541524	062964415245	10M ORANGE 16/3	1/12
WD-541550	062964415504	15M ORANGE 16/3	1/10

Triple Tap Indoor Clear w/ Indicator

- safely converts 1-outlet into 3 • bar mounts horizontally on the outlet • clear case includes an LED power indicator light • for indoor use • grounded male plug and female outlets

IIIWoods®



Item #	UPC	Description	Pack
WD-546322	062964463222	3-OUTLET ADAPTOR	1/10

HD Outdoor Cord 3-Outlet/ 3-Conductor

- copper conductors • solid molded plug • 3 outlets • 2 layers of insulation • resists deterioration from moisture & abrasion • 300V • run 2 to 3 tools at once • wire gauge: 14-3 • wire type: SJTW • CSA approved • red cord

IIIWoods®



Item #	UPC	Description	Pack
WD-545609	062964456095	10M RED 14/3	1/13
WD-545612	062964456125	15M RED 14/3	1/8
WD-545625	062964456255	30M RED 14/3	1/3

Power Post 3-Outlet w/ Photo Electric Timer

- temporary outdoor power supply • 3-timer controlled outlets on a stake • 2-modes for timer - dusk to dawn or timed setting from 2-8 hours • photo electric eye turns lights on/off • same time setting each day • 6' HD 3-prong cord • clear, rain tight housing protects controls • replaces WD-45942

IIIWoods®



Item #	UPC	Description	Pack
WD-49028	062964490280	POWER POST PHOTO ELECTRIC	1/8

TRADESMAN Power Block Cord 3-Outlet

- copper conductors • solid molded plug • 3 outlets • 2 layers of insulation • resists deterioration from moisture & abrasion • 600V • non-marking coating • wire gauge: 12-3 • wire type: STW • CSA approved • yellow cord

IIIWoods®



Item #	UPC	Description	Pack
WD-545650	062964456507	1M YELLOW 12/3 (REPL WD-10824)	1/6

HIGH VISIBILITY SAFETY CORDS

High Visibility Safety Cord 1-Outlet

• copper conductors • solid molded plug • single outlet • 2 layers of insulation • resists deterioration from moisture & abrasion • 300V • non-marking coating • wire gauge: 14-3 • wire type: SJTW • CSA approved • yellow/black cord



Item #	UPC	Description	Pack
WD-510521	062964105214	15M14/3 (REPL. WD-10521)	1/8
WD-510522	062964105221	30M 14/3 (REPL. WD-10522)	1/3

LANDSCAPE CORDS

Landscape Cord - Green 1-Outlet

• light duty • copper conductors • solid molded plug • single outlet • 2 layers of insulation • resists deterioration from moisture & abrasion • 300V • non-marking coating • wire gauge: 16-3 • wire type: SJTW • CSA approved • green cord



Item #	UPC	Description	Pack
WD-550393	062964503935	12M GREEN 16/3	1/12
WD-550394	062964503942	24M GREEN 16/3	1/6

HD High Visibility Safety Cord 1-Outlet

• copper conductors • solid molded plug • single outlet 3-Conductor • 2 layers of insulation • resists deterioration from moisture & abrasion • 300V • non-marking coating • wire gauge: 12-3 • wire type: SJTW • CSA approved • yellow/black cord



Item #	UPC	Description	Pack
WD-550523	0629644505236	15M 12/3 (REPL. WD-10523)	1/6
WD-550524	0629644505243	30M 12/3 (REPL. WD-10524)	1/3

Promotional Garden Cords 1-Outlet

• copper conductors • solid molded plug • single outlet • 2 layers of insulation • resists deterioration from moisture & abrasion • 300V • non-marking coating • wire gauge: 16-3 • wire type: SJTW • CSA approved • yellow cord



Item #	UPC	Description	Pack
WD-542107	062964421079	15M YELLOW 16/3(REPL WD-10263)	1/10
WD-542111	062964421116	25M YELLOW 16/3(REPL WD-10264)	1/6

BLOCK HEATER CORDS

Block Heater Cord -30° 3-Outlet

• medium duty • SJTW cord 3-outlet plug • grounded • durable, certified waterproof, resists UV rays • great for block heaters, battery blankets, car warmers, etc • wire gauge: 16-3 • CSA approved • blue cord • flexible to -30°C



Item #	UPC	Description	Pack
WD-545332	062964453322	3M BLUE 16/3	1/32
WD-545340	062964453407	5M BLUE 16/3	1/21

Medium Duty Coldflex Cord 3-Outlet

• medium duty • SJTW cold flex wire • 3-conductor • 3 outlets • stays flexible to -50°C • female ends won't constrict making it easy to plug/unplug in extreme cold • blue male and female ends • wire gauge: 16-3 • CSA approved • blue cord



Item #	UPC	Description	Pack
WD-510844	062964108444	3M BLUE 16/3	1/32
WD-510845	062964108451	5M BLUE 16/3	1/21
WD-510846	062964108468	10M BLUE 16/3	1/12
WD-510847	062964108475	15M BLUE 16/3	1/10

Extra Heavy Duty Coldflex Cord 1-Outlet

- extra heavy duty SJTW cold flex wire • stays flexible to -50°C • female ends won't constrict making it easy to plug/unplug in extreme cold • blue male and female ends • wire gauge: 12-3 • CSA approved • blue cord



Item #	UPC	Description	Pack
WD-510668	062964106686	8M BLUE 12/3	1/10
WD-510669	062964106693	15M BLUE 12/3	1/6
WD-510670	062964106709	30M BLUE 12/3	1/3

Super Flex Cord With Power Indicator 3-Outlet Block

- exclusive high-gloss super flexible wire • 3-outlet adapter • high impact molded power block head • PowerLite™ plug • clear power indicator outlet shows power in cord • wire gauge: 12-3 • wire type: SJTW • flexible at any temperature • CSA approved • yellow cord



Item #	UPC	Description	Pack
WD-510023	062964100233	8M YELLOW 12/3	1/10
WD-510019	078693100192	15M YELLOW 12/3	1/6
WD-510020	078693100208	30M YELLOW 12/3	1/3

Polar Winterflex Cords with powerlite 3-Outlet

- tested to stay flexible to -50° • 3 female outlets with power indicator light • female outlets will not constrict making it easy to plug and unplug male ends after prolonged exposure to extreme cold • black color cord • 16/3 STOW cable is resistant to oil and fuel



Item #	UPC	Description	Pack
WD-545337	062964453377	2M BLACK 16/3	1/32
WD-545338	062964453384	5M BLACK 16/3	1/21
WD-545339	062964453391	10M BLACK 16/3	1/12

HD Cord with GFCI, Powerlite 1-Outlet

- Ground Fault Circuit Interrupter(G.F.C.I.) protected • PowerLite™ plug • clear power indicator outlet shows power in cord • wire gauge: 12-3 • wire type: SJTW premium • CSA approved • yellow cord



Item #	UPC	Description	Pack
WD-510077	078693100772	1M YELLOW 12/3(REPL WD-10077)	1/10

SuperFlex Cord with Power Indicator 1-Outlet

- exclusive high-gloss super flexible wire • PowerLite™ plug • clear power indicator outlet shows power in cord • wire gauge: 14-3 • wire type: SJTW premium • CSA approved • yellow cord



Item #	UPC	Description	Pack
WD-550086	062964100868	8M YELLOW 14/3	1/13
WD-550087	078693100871	15M YELLOW 14/3	1/8
WD-550088	078693100888	30M YELLOW 14/3	1/3

Power Block SuperFlex Cord Powerlite 3-Outlet

- exclusive high-gloss super flexible wire • 3-outlet adapter • high impact molded power block head • PowerLite™ plug • clear power indicator outlet shows power in cord • wire gauge: 14-3 • wire type: SJTW premium • flexible at any temperature • CSA approved • yellow cord



Item #	UPC	Description	Pack
WD-510110	062964101100	8M YELLOW 14/3	1/13

CORD MANAGEMENT

NOMA Self-Storing Cord Caddy 10M

- durable polyethylene housing • self storing extension cord • 4 grounded outlets • overload protection with built in 10A circuit breaker protects tools • easy wind • SJTW 16/3 10-Amp cord • allows 4 tools or appliances to be plugged in



Item #	UPC	Description	Pack
WD-545794	062964457948	10M ORANGE 16/3	1/6

Twin Cleat™ Cord Lock

- tough & durable with no loose parts • no screws or adjustments • works with 14 & 16-gauge cords • replaces WD-2804



Item #	UPC	Description	Pack
WD-502804	062964028049	CORD LOCK	1/12

7.5M Power Caddy+™

- high impact plastic case • 4 grounded outlets • 10A circuit breaker • easy rewinding • power indicator light • convenient mounting holes • includes 7.6m 16-3 black SJTW extension cord • replaces WD-2801



Item #	UPC	Description	Pack
WD-502801	062964028018	7.6M BLACK 16/3	1/6

Poly Carry Strap

- poly one-piece construction • adjustable • large molded handle • holds up to 45m of 16/3cords • can be used to store holiday string lights • replaces WD-2802



Item #	UPC	Description	Pack
WD-502805	062964028056	CORD CARRY STRAP	1/32

Cord Caddy

- rugged plastic one-piece construction • convenient carrying handle • hang up holes for easy storage • replaces WD-2803



Item #	UPC	Description	Pack
WD-502803	062964028032	CORD CADDY	1/12

Basic Plug Bars For Home Electronics 6-Outlet

- provides basic protection from dangerous spikes and energy surges • plastic housing • built-in circuit breaker • on/off switch • protection for surges to 6000V • EMI/RFI added protection



Item #	UPC	Description	Pack
WD-545101	062964451014	3' CORD 312-JOULE (REPLWD-0418)	1/12
WD-545243	062964452431	4' CORD 210-JOULE(REPL.WD-0425)	1/12

Mini Indoor Cord Wraps

- ideal for organizing your home or office cords • no more tangles • stores indoor cords, holiday lights etc. • holds cords up to 4.5m(15') or small strands of holiday lights • white plastic • come 2 wraps on a card



Item #	UPC	Description	Pack
WD-147656	062964476567	2/CARD WHITE	1/20

1-Way Superior Surge Protection 1-outlet

- ideal for electronics, appliances and office equipment • shutdown protection • advanced power filtration technology • ground and surge indicator light • 1-outlet ideal for fireplaces, microwaves • 125V 15A 1875W • max spike voltage 6000V • current 40,000-amp



Item #	UPC	Description	Pack
WD-546500	062964465004	1-OUTLET 810-JOULE	1/12

1-Way Superior Surge Protection 7-outlet

- ideal for electronics, appliances and office equipment • shutdown protection • advanced power filtration technology • 7-outlet has rotatable outlet covers • ground and surge indicator light • adjustable, cord management



Item #	UPC	Description	Pack
WD-546506	062964465066	7-OUTLET 6' CORD 1085-JOULE	1/8

ELECTRICAL CONVENIENCE - WORKSHOP

8-Outlet Power Center Timer Controlled

- all-in-one timer and power bar with 8-grounded outlets • 4' cord • 24-hour cycle timer • up to 48-on/off settings per day • "never-lose" pins • slide safe outlet covers • 4-outlets controlled by timer and 4 controlled by switch • override allows you to turn lights on/off at any time



Item #	UPC	Description	Pack
WD-148174	062964481745	TIMER / POWER BAR	1/4

Pro Power Workshop Bar 4-Outlet

- heavy gauge steel case with built-in circuit breaker • 3-conductor plug • 4 grounded outlets • 1.2m cord • black • replaces WD-2177



Item #	UPC	Description	Pack
WD-502177	062964021774	4-OUTLET BLACK	1/5

Pro Power 8-Outlet Metal Shop Bar

- 8-grounded outlets • 5-standard spaced outlets and 3 wide spaced outlets • heavy duty metal housing • rear mounting holes • convenient on/off switch • built-in cord management • extra tough for workshop jobs • 6' yellow cord with grounded male plug



Item #	UPC	Description	Pack
WD-546161	062964461617	WORKSHOP BAR	1/6

CLAMP & BROODER/HEAT LAMPS

Flood & Clamp Lamp


- made with tough, heat resistant non-metallic socket • aluminum reflector • push through switch • fully adjustable sturdy metal spring clamp that swivels • jaw is vinyl coated and opens 4.5cm • vinyl grip • polarized male plug • 2m white cord • CSA approved



Item #	UPC	Description	Pack
WD-510160	062964101605	5-1/2" 60W 18/2	1/8
WD-510151	062964101513	8-1/2" 150W 18/2(REPL. WD10151)	1/5

Brooder & Heat Lamp

- insulated heavy duty porcelain socket • 10" heavy gauge aluminum reflector • hang-up hooks • bulb guard which snaps on the reflector • 18/2 SPT-2 wire • polarized male plug • 1.8m black socket cord • CSA approved • ideal for farm + pet



Item #	UPC	Description	Pack
WD-510166	062964101667	10" W/ CLAMP 18/2	1/12

Clamp Lamp with Porcelain Socket

- great for projects where high heat is required • heat resistant porcelain socket • no reflector • maximum bulb 300-watts • polarized male plug • push through switch • strong double swivel clamp • sturdy metal spring clamp • jaws open to 4.5cm and are vinyl covered • black cord is 1.8m long • 18/2 SPT-1 cable • replaces wd-cl7250



Item #	UPC	Description	Pack
WD-546712	062964467121	1.8M BLACK 18/2	1/20

PLASTIC OUTDOOR GARDEN LIGHTING

Noma Floodlight Kits

- built-in outlet • weather resistant durable plastic • non slip angle adjustment • includes safety socket • cord, ground spike, baseplate for wall mounting • flood light bulb



Item #	UPC	Description	Pack
WD-12112	062964121122	CLEAR	1/10

Noma Floodlight Kits

- built-in outlet • weather resistant durable plastic • non slip angle adjustment • includes safety socket • cord, ground spike, baseplate for wall mounting • flood light bulb

Woods®



Item #	UPC	Description	Pack
WD-12113	062964121139	RED	1/10
WD-12114	062941211464	BLUE	1/10
WD-12115	062964121153	GREEN	1/10
WD-12116	062964121160	YELLOW	1/10

TROUBLE LIGHTS

Trouble Light

- dual hook system • polarized • heat resistant • on/off switch • hard wearing cord with 2 layers of insulation • maximum 100W bulb (Not Included) • metal cage • wire gauge: 18-2 • CSA approved • orange cord

Woods®



Item #	UPC	Description	Pack
WD-541329	062964413296	1M ORANGE 18/2	1/12
WD-541332	062964413326	6M ORANGE 18/2	1/10
WD-541362	062964413623	10M ORANGE 18/2	1/9
WD-541388	062964413883	15M ORANGE 18/2	1/6

Noma Plastic Floodlight Single Socket

- built-in outlet • weather resistant durable plastic • non slip angle adjustment • 1 socket • 2 mounting options wall/deck plate or ground stake

Woods®



Item #	UPC	Description	Pack
WD-12357	062964123577	SINGLE SOCKET	1/10

Heavy Duty Trouble Light with Receptacle Handle

- dual hook system • polarized • heat resistant • on/off switch • hard wearing cord with 2 layers of insulation • maximum 100W bulb (Not Included) • metal cage • receptacle in handle • wire gauge: 16/3 • CSA approved • blue cord

Woods®



Item #	UPC	Description	Pack
WD-541426	062964414262	10M BLUE 16/3	1/9
WD-541455	062964414552	15M BLUE 16/3	1/6

Noma Plastic Floodlight Double Socket

- built-in outlet • weather resistant durable plastic • non slip angle adjustment • 2 sockets • 2 mounting options wall/deck plate or ground stake

Woods®



Item #	UPC	Description	Pack
WD-12355	062964123553	DOUBLE SOCKET	1/10

ELECTRICAL POWER ACCESSORIES

Portable PowerLite PI plugs

- Plugs into any 3 conductor extension cord or wall outlet • shows at a glance if the power is ON • 2 plugs per pack • 15A/125V/1875w • ideal for freezers, appliances, pumps, power tools, etc

Woods®



Item #	UPC	Description	Pack
WD-512521	062964125212	POWERLITE	1/18

Portable Slide Dimmer Switch 9' (2.7m) Cord

- easily adjusts holiday decorations or indoor lighting • polarized 2-prong outlet • red indicator (LED) light shows if lamp is on or off • dim lights for ambiance and save energy • 2.5A, 120V, 300W • 9' cord

Woods®



Item #	UPC	Description	Pack
WD-149542	062964495421	PORTABLE DIMMER	1/12

Indoor HD 7-Day Grounded Digital Timer

- 7-day cycle • can set different programs for each different day of the week • 2-outlets • program 2 appliances at once • daily setting works both outlets • outlets are grounded 3-prong • 15A/1875W resistive • 5A/600W tungsten • 1/2HP • replaces WD-TD1101 • (TD1300-2)

Woods®



Item #	UPC	Description	Pack
WD-49556	062964495568	I/D HD DIGITAL TIMER	1/12

Yellow Jacket Plug-In GFCI + Surge Protector

- portable inline GFCI protection (ground fault circuit interruption) • also provides surge protection • test and reset buttons • convenient, portable size • 15A/120V/1800W • powerlite indicator end

Woods®



Item #	UPC	Description	Pack
WD-582762	078693027628	GFCI/SURGE (REPL. WD-82762)	1/6

H.D. Grounded 7-Day Digital Timer w/ 2 Outlets

- 7-day cycle • 8-on/off per day (56 per week) • set for individual days or 1 of 8 presets • sleep count down • manual override • 2 convenient side outlets • 3 prong grounded plug and receptacles • 1875W, 15Amp, 1HP • easy push button settings • self charging battery backup • replaces WD-TD2200

Woods®



Item #	UPC	Description	Pack
WD-49377	062964493779	7-DAY DIGITAL HD 56/WEEK	1/6

MECHANICAL INDOOR TIMERS

Indoor 24-Hour Lighting Timer

- 24-hour model cycles same times each day • color coded setting pins • child safe pins can only be released if center button is depressed • use with lamps, holiday lights, radios and more • 2-prong polarized plug and receptacle • 2-on/off settings per day • 30-minute interval settings • 15A/1875W resistive • replaces WD-T1000, WD-T2001

Woods®



Item #	UPC	Description	Pack
WD-49528	062964495285	2 ON/OFF SETTINGS	1/12

MECHANICAL OUTDOOR TIMERS

Light Duty Outdoor Mechanical Timer

- promotional outdoor mechanical timer • up to 24 settings operate same each day • durable weatherproof construction • child safe "never lose" pins • ideal for outdoor lighting • rated 1250W, 10-amp • grounded plug • replaces WD-TM1710

Woods®



Item #	UPC	Description	Pack
WD-49109	062964491096	24 HOURS 24/DAY	1/3

Heavy Duty Indoor Appliance Timer

- heavy duty appliance timer • 24 on/off settings per day • 30-minute interval settings • grounded 3-prong outlet • ideal for air conditioners, heaters, heavy duty lamps and appliances • 15A/1875W resistive • 8A/1000W tungsten • never lose pins • replaces WD-T3000, WD-T3001

Woods®



Item #	UPC	Description	Pack
WD-49529	062964495292	24-HOUR HD TIMER	1/12

HD Outdoor Mechanical Timer

- heavy duty 1-HP rating • weather proof and durable with a protective cover • child safe "never lose" pins • ideal for outdoor lights, car heaters, pool pumps, etc. • grounded plug • 1875W, 15-amp • 1-HP • available in 24-hour and weekly settings • replaces WD-TM1702

Woods®



Item #	UPC	Description	Pack
WD-49382	062964493823	24HR HD 48/DAY	1/6

Outdoor HD 7-Day Grounded Mechanical Timer

- 7-day timer allows different programs each day • manual override buttons • easy to read digital display • battery backup protects program in power failures • random settings for security • grounded 3-prong outlet • controls heavy duty loads pool/spa pumps, block heaters, motors etc. • 15A/1875W resistive • 8A/1000W tungsten • *replaces WD-N1507*

Woods®



Indoor/Outdoor Wireless Remote Switch

- remote control works as an on/off switch without wiring • 30' range • signal works through walls and doors • for indoor or outdoor use • 2-outlets • ideal for lamps, holiday lights, etc • control outdoor lighting from the comfort of indoors • 15A/1875W resistive • 8A/1000W tungsten • *replaces WD-WRS220*

Woods®



Item #	UPC	Description	Pack
WD-49565	062964495650	O/D HD DIGITAL TIMER	1/6

Item #	UPC	Description	Pack
WD-49063	062964490631	2-OUTLET WHITE R/C	1/6

PHOTOELECTRIC O/D

Outdoor 24-Hour Photoelectric Lighting Timer

- photocell electric eye automatically turns lights on at dusk • program options to turn lights out in 1-9 hours • same on/off settings for each day • electronic display on 1/2" screen shows hours selected • weatherproof for outdoor • polarized 2-prong outlet with polarized plug • *replaces WD-N1502*

Woods®



Outdoor 24-Hour Timer Remote w/ 2-Outlets

- automatically turns lights on at dusk and off at dawn • electronic timer also has 2-8 hours settings • 2-outlets just plug in • grounded 3-prongs • wireless remote controls lights & appliances up to 50' away • great for holiday lighting, lamps, appliances etc.

Woods®



Item #	UPC	Description	Pack
WD-49103	062964491003	O/D TIMER 24-HOUR	1/5

Item #	UPC	Description	Pack
WD-49544	062964495445	R/C OUTDOOR TIMER	1/10

Outdoor 24-Hour All Purpose / Block Heater Timer

- simple 2-button programming • 2-digit LED display shows time to the nearest hour • 3-Prong grounded plug and outlet • same on/off each day • durable weather proof construction • ideal for block heaters, car warmers, security lights, holiday lights, etc. • *replaces WD-1506N*

Woods®



Item #	UPC	Description	Pack
WD-49122	062964491171	24-HOUR TIMER	1/5

REMOTE CONTROL TIMERS

Indoor / Outdoor 1-Outlet Wireless Remote Outlet

- remote control works as an on/off switch without wiring • turns lights or appliances on/off up to 24m/80' away • signal works through walls and doors • indoor or outdoor use • 1-outlet grounded • operates lamps, small appliances, holiday lighting etc. • 13A/1625W resistive • 8A/1000W tungsten

Woods®



Item #	UPC	Description	Pack
WD-49568	062964495681	1-OUTLET BLACK R/C SWITCH	1/10