



# Pilot devices - compact 22mm

## Selector switches

Compact range




### Selector switches 2 position BLACK plastic bezel



Type	Contacts		Part Number	Product Hierarchy 1300001 Order Code
	N/O	N/C		
Stay Put -BC	1	0	C2SS1-10 ■-10	1SFA619200R101 □
	2	0	C2SS1-10 ■-20	1SFA619200R102 □
	0	1	C2SS1-10 ■-01	1SFA619200R104 □
	0	2	C2SS1-10 ■-02	1SFA619200R105 □
	1	1	C2SS1-10 ■-11	1SFA619200R107 □
Stay Put -AC	1	0	C2SS2-10 ■-10	1SFA619201R101 □
	2	0	C2SS2-10 ■-20	1SFA619201R102 □
	0	1	C2SS2-10 ■-01	1SFA619201R104 □
	0	2	C2SS2-10 ■-02	1SFA619201R105 □
	1	1	C2SS2-10 ■-11	1SFA619201R107 □
Spring Return -BC	1	0	C2SS3-10 ■-10	1SFA619202R101 □
	2	0	C2SS3-10 ■-20	1SFA619202R102 □
	0	1	C2SS3-10 ■-01	1SFA619201R104 □
	0	2	C2SS3-10 ■-02	1SFA619202R105 □
	1	1	C2SS3-10 ■-11	1SFA619202R107 □

### Selector switches 3 position BLACK plastic bezel



Stay Put -ABC	2	0	C3SS1-10 ■-20	1SFA619210R102 □
	0	2	C3SS1-10 ■-02	1SFA619210R105 □
	1	1	C3SS1-10 ■-11	1SFA619210R107 □
Spring return -ABC	2	0	C3SS2-10 ■-20	1SFA619211R102 □
	0	2	C3SS2-10 ■-02	1SFA619211R105 □
	1	1	C3SS2-10 ■-11	1SFA619211R107 □
Spring return -CB stay put A	2	0	C3SS3-10 ■-20	1SFA619212R102 □
	0	2	C3SS3-10 ■-02	1SFA619212R105 □
	1	1	C3SS2-10 ■-11	1SFA619212R107 □
Spring return -AB stay put C	2	0	C3SS7-10 ■-20	1SFA619216R102 □
	0	2	C3SS7-10 ■-02	1SFA619216R105 □
	1	1	C3SS7-10 ■-11	1SFA619216R107 □

#### Order example:

Ex1: Type CP1-10 ■-10, to order colour red replace ■ with R: CP1-10 R-10

Ex2: Order code 1SFA619100R101□

To order red replace □ with 1: 1SFA619100R1011


#### Colour Codes

	Red	Black	Grey
Type ■	R	B	U
Order code □	1	6	7


# Pilot devices - compact 22mm

## Selector switches


Compact range



### Selector switches 2 position CHROME metal bezel



Type	Contacts		Part Number	Product Hierarchy 1300001 Order Code
	N/O	N/C		
Stay Put -BC	1	0	C2SS1-30 ■-10	1SFA619200R301□
	2	0	C2SS1-30 ■-20	1SFA619200R302□
	0	1	C2SS1-30 ■-01	1SFA619200R304□
	0	2	C2SS1-30 ■-02	1SFA619200R305□
	1	1	C2SS1-30 ■-11	1SFA619200R307□
Stay Put -AC	1	0	C2SS2-30 ■-10	1SFA619201R301□
	2	0	C2SS2-30 ■-20	1SFA619201R302□
	0	1	C2SS2-30 ■-01	1SFA619201R304□
	0	2	C2SS2-30 ■-02	1SFA619201R305□
	1	1	C2SS2-30 ■-11	1SFA619201R307□
Spring Return -BC	1	0	C2SS3-30 ■-10	1SFA619202R301□
	2	0	C2SS3-30 ■-20	1SFA619202R302□
	0	1	C2SS3-30 ■-01	1SFA619201R304□
	0	2	C2SS3-30 ■-02	1SFA619202R305□
	1	1	C2SS3-30 ■-11	1SFA619202R307□



### Selector switches 3 position CHROME plastic bezel

Stay Put -ABC	2	0	C3SS1-30 ■-20	1SFA619210R302 □
	0	2	C3SS1-30 ■-02	1SFA619210R305 □
	1	1	C3SS1-30 ■-11	1SFA619210R307 □
Spring return -ABC	2	0	C3SS2-30 ■-20	1SFA619211R302 □
	0	2	C3SS2-30 ■-02	1SFA619211R305 □
	1	1	C3SS2-30 ■-11	1SFA619211R307 □
Spring return -CB stay put A	2	0	C3SS3-30 ■-20	1SFA619212R302 □
	0	2	C3SS3-30 ■-02	1SFA619212R305 □
	1	1	C3SS2-30 ■-11	1SFA619212R307 □
Spring return -AB stay put C	2	0	C3SS7-30 ■-20	1SFA619216R302 □
	0	2	C3SS7-30 ■-02	1SFA619216R305 □
	1	1	C3SS7-30 ■-11	1SFA619216R307 □

#### Order example:

Ex1: Type CP1-10 ■-10, to order colour red replace ■ with R: CP1-10 R-10

Ex2: Order code 1SFA619100R101□

To order red replace □ with 1: 1SFA619100R1011

#### Colour Codes

	Red	Black	Grey
Type ■	R	B	U
Order code □	1	6	7