

CP1-12G-10



PUSHBUTTON#CP1-12G-10#110-130V AC

General Information

Extended Product Type	CP1-12G-10
Product ID	1SFA619100R1212
EAN	7320500381526
Catalog Description	PUSHBUTTON#CP1-12G-10#110-130V AC
Long Description	Compact Pushbutton - Momentary - Flush - Green - Illuminated - Black plastic - 1NO

Ordering

EAN	7320500381526
Minimum Order Quantity	10 piece
Customs Tariff Number	85369001

Dimensions

Product Net Width	0.030 m
Product Net Height	0.030 mm
Product Net Depth / Length	0.055 m
Product Net Weight	0.018 kg

Environmental

Ambient Air Temperature	Operation -25 ... +70 °C
RoHS Status	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Additional Information

Actuator Type	Flush
Additional Information	III. PB
Bezel Material	Black plastic
Block	1NO
Color	Green
Degree of Protection	Front IP69K Terminals IP20
Function	Momentary
Illumination	Illuminated
Lamp Type	LED 110-130V AC

Lens Color	Green
Lower Button Color	Green
Mechanical Durability	0.5 million
Number of Auxiliary Contacts NC	0
Number of Auxiliary Contacts NO	1
Order Multiple	1 piece
Product Main Type	CP1
Product Name	Pushbutton
Product Range	Compact
Product Type	CP
Rated Frequency (f)	50 / 60 Hz
Rated Operational Current AC-15 (I _{th})	(240 V AC) 1 A
Rated Operational Current DC-13 (I _{th})	(24 V) 0.3 A (125 V) 0.2 A
Rated Operational Voltage	110 ... 130 V AC/DC
RoHS Date	0626 5

Certificates and Declarations (Document Number)

Data Sheet, Technical Information	1SFC151005C0201
Declaration of Conformity - CE	1SFA1-70
Environmental Information	1SFC151009D0201
Instructions and Manuals	1SFC151005C0201
RoHS Information	1SFC151012D0202

Classifications

E-nummer	3717262
ETIM 4	EC002024 - Accessories for control circuit devices
ETIM 5	EC001028 - Push button, complete
ETIM 6	EC001028 - Push button, complete
ETIM 7	EC001028 - Push button, complete
Object Classification Code	S
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Low Voltage Products and Systems → Control Products → Pilot Devices → Pilot Devices - Compact Range

