SATCO | NUVO

Project Name

Location	Prepared By

SATCO S11637

11WLED/DW/6/RGBTW/RND/WH

Notes

[www] 10-27-2025 05:20:49

General

Status	Active
Finish	White
Wattage	11W
CCT (Kelvin)	2000K-5000K
Color Temperature	RGB and Tunable White
Width (in.)	7.17
Height (in.)	1.02
Indoor or Outdoor Fixture	Indoor and Outdoor

Smart Product Info

IOT Enabled	Yes
Integrated Camera	No
Software Upgradeable	Yes
Communication Protocol	WiFi-2.4GHz
Voice Assistants Supported	Alexa; Google Home; Siri; SmartThings
Software Supported	Tuya/Starfish APP

Specifications

Technology	LED
CRI	90+
Lumen Output	900L
Rated Hours	50000
Voltage	120V
Dimmable	Yes-Dimmable
Dimming Note	Only with Starfish App
Beam Angle	110
Operating Temperature	-40C (-40F) to +50C (+122F)
IC Rated	Yes
Weight (lb.)	1.17
Fixture Shape	Round
Fixture Material	Aluminum
Fixture Type	Downlight

Compliance

Safety Listing	cETLus
Location Rating	Wet
ENERGY STAR	Pending
Air Tight Rated	Yes
California Status	Lawful for sale in California
Title 20 / 24 Status	Lawful for sale
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
Canadian Standard ICES-005	Class B

Additional Information

Warranty	5-Years

Copyright 2023 Satco Products, Inc.
All Rights Reserved

For More Information Visit:
https://www.satco.com/