SCPT

CONSTANT WATTAGE PIPE FREEZE PROTECTION HEATING CABLE



2 YEAR WARRANTY

SAY GOODBYE TO FROZEN PIPES

This preassembled heating cable is designed to prevent pipes from freezing and avoid water damage. The cable is easy to install thanks to its 120 V plug, and the integrated thermostat triggers heat only when necessary. The cable is installed on pipes under insulation and protects against freezing down to -40 °C (-40 °F). Ideal for metal or plastic pipes up to 1.5 in. (3.81 cm) in diameter.*

- **PREVENTS PIPE BREAKAGE AND WATER DAMAGE**
- **IDEAL FOR PLASTIC OR METAL PIPES**
- **LIGHTED PLUG POWER INDICATOR**
- **INTEGRATED THERMOSTAT THAT TRIGGERS AT 3 °C (37 °F) TO PREVENT FREEZING**

IDEAL FOR:

pipes at risk of freezing

QUICK AND EASY PLUG-IN INTO 120 V OUTLET

MANUFACTURING

- tough XLPE inner insulation
- AL foil and continuous ground braid
- weather resistant PVC (high-low temperature) out jacket
- twin conductor
- bending radius of 1 inch
- 2 ft cold lead with plug

WATTAGE

- 7 W/ft

CONTROL

- built-in thermostat

INSTALLATION

- install at a temperature above -10 °C (14 °F)

WARRANTY

- two years

*The cable must never cross over itself. Plastic pipes must always be filled with water.

TECHNICAL SPECIFICATIONS

PRODUCT	LENGTH	VOLTAGE	POWER	AMPERAGE
CODE	FT	VOLTS	WATTS	AMPS
SCPT1W0021L0003	3	120	21	0.2
SCPT1W0042L0006	6	120	42	0.4
SCPT1W0063L0009	9	120	63	0.5
SCPT1W0084L0012	12	120	84	0.7
SCPT1W0105L0015	15	120	105	0.9
SCPT1W0126L0018	18	120	126	1.1
SCPT1W0168L0024	24	120	168	1.4
SCPT1W0210L0030	30	120	210	1.8
SCPT1W0280L0040	40	120	280	2.3
SCPT1W0420L0060	60	120	420	3.5

FC_SCPT_EN_150925

°STELPRO

Stelpro reserves the right to modify at any time the description, manufacturing, or price of its products. Additionally, Stelpro may apply restocking fees or refuse a refund based on one or more of the following criteria: optional color, custom product, assembly with low-demand options. For the latest product information and prices regarding the products, please visit the website www.stelpro.com.



Stelpro reserves the right to modify at any time the description, manufacturing, or price of its products. Additionally, Stelpro may apply restocking fees or refuse a refund based on one or more of the following criteria: optional color, custom product, assembly with low-demand options. For the latest product information and prices regarding the products, please visit the website www.stelpro.com.