















Project: _____

Fixture Type: _____

Location: _____

Contact/Phone: _____

Trim Series	Dimensions	Aperture	Catalog No.	Housing / Lamp Compatibility
 Decorative Swirled Etched Opal Glass			243 WH 6" Decorative Swirled Etched Opal Glass Trim - White *Do not use reflector shipped with trim for LED housing	IC2: 60W A19 TC2/TC2R: 100W A19 IC22LED*: G4 06LM, WD G4N 06LM/G4 09LM, WD G4 09LM/ G4 14LM IC22RLED*: G4 06LM, WD G4N 06LM/G4 09LM, WD G4 09LM TC22LED*: G4 09LM/G4 14LM/ G4 20LM ICPL6: 18W, 26W, 32W PL6: 18W, 42W (32W rating)
 Metal Band		5-7/8"	9524 SC 6" Decorative Metal Band Trim - Satin Chrome	IC2/TC2/TC2R: 65W BR30 IC22/IC22 W/IC22 S/IC22R: 50W PAR30, 75W PAR30L, 65W BR30 IC22LED: G4 06LM, WD G4N 06LM/G4 09LM, WD G4 09LM/ G4 14LM IC22RLED: G4 06LM, WD G4N 06LM/G4 09LM, WD G4 09LM TC22LED: G4 09LM/G4 14LM/ G4 20LM APT2: 65W BR30
 Luminous Disc (Frosted)		3-1/4"	9324 SC 6" Decorative Luminous Frosted Disc Trim - Satin Chrome	IC2/TC2/TC2R: 65W BR30 IC22/IC22 W/IC22 S/IC22R: 50W PAR30, 75W PAR30, 65W BR30 IC22LED: G4 06LM, WD G4N 06LM/G4 09LM, WD G4 09LM/ G4 14LM IC22RLED: G4 06LM, WD G4N 06LM/G4 09LM, WD G4 09LM TC22LED: G4 09LM/G4 14LM/ G4 20LM APT2: 65W BR30
 Fluted Drop Opal			9900 WH 6" Wall Wash Fluted Drop Opal Trim - White	IC2: 60W A19 TC2/TC2R: 75W A19 ICPL6: 18W, 26W, 32W PL6: 18W, 42W (26W rating) APT2: 75W A19
 Octagonal		5-3/4"	9024 WWH 6" Decorative Octagonal Trim - White, White Trim Ring	IC2/TC2/TC2R: 65W BR30 IC22/IC22 W/IC22 S/IC22R: 50W PAR30, 65W BR30 IC22LED: G4 06LM, WD G4N 06LM/G4 09LM, WD G4 09LM/ G4 14LM IC22RLED: G4 06LM, WD G4N 06LM/G4 09LM, WD G4 09LM TC22LED: G4 09LM/G4 14LM/ G4 20LM APT2: 65W BR30
 Luminous Collar (Frosted)		6-3/8"	9702 6" Decorative Luminous Frosted Collar Trim - Luminous Collar (Frosted)	IC2/TC2/TC2R: 65W BR30 IC22/IC22 W/IC22 S/IC22R: 50W PAR30, 75W PAR30L, 65W BR30 IC22LED: G4 06LM, WD G4N 06LM/G4 09LM, WD G4 09LM/ G4 14LM IC22RLED: G4 06LM, WD G4N 06LM/G4 09LM, WD G4 09LM TC22LED: G4 09LM/G4 14LM/ G4 20LM APT2: 65W BR30

Housing and trim can be ordered together or separate, but will always ship separately.