

Hinged Par-Tech

Lytespan line voltage

Features a modular adapter that can stand alone or be used with a bezel, cone or cylindrical shade available in three sizes. A hinged, chrome-plated steel lever cradles the lamp holder and permits adjustment up to 90° from vertical. Die-cast aluminum shades with bayonet mount attach with simple twist-action. Shades hug the lamp profile and may be used with hex cell louver, beam elongator and beam smoother; barn doors for PAR16, 20, or 30 bezel only.

For Accessories see page 2.8.



Hinged adapter



8202WH

8202BK

R20, 75W max.

R30, 100W max.


PAR16, 75W max.

PAR20, 50W max.

PAR30, 75W max.

PAR38, 75W max.

PAR16 Bezel shade



8202WH/8217WH

8202BK/8217BK


PAR16 60W max.

Accessory holder: 8591

Accessories: One AF2 diffusion, ADF2 color filter series.

Note: Not for use with AL2HC.

PAR20 Bezel shade



8202WH/8227WH


8202BK/8227BK

PAR20, 50W max.

Accessory holder: 8592

Accessories: One AF25 diffusion, ADF25 color filters, AL25 series., 8542BK

PAR30 Bezel shade



8202WH/8237WH


8202BK/8237BK

PAR30, 75W max.

Accessory holder: 8593

Accessories: One AF3, ADF3 or AL3 series., 8543BK

PAR38 Bezel shade




8202WH/8247WH

PAR38 150W max.

Accessory holder: 8595

Accessories: Two AF4, ADF4 or AL4 series.

PAR20 Mesh shade




8202WH/8229WH

8202BK/8229BK

PAR20 50W max.

PAR30 Mesh shade



8202WH/8239WH

8202BK/8239BK

PAR30 75W max.

Symbol indicates compatibility with extension wands, sloped ceiling adapter and clamp-on monopoint.

PAR16 Cone shade




8202WH/8215WH
8202BK/8215BK
PAR16 75W max.

Accessory holder: 8581

Accessories: Two AF2 or ADF2 series.
(60W max. w/accessories)

Note: Not for use with AL2HC.

PAR20 Cone shade




8202WH/8225WH
8202BK/8225BK
PAR20 50W max.

Accessory holder: 8582

Accessories: Two AF25 diffusion,
ADF25 or AL25 series.

PAR30 Cone shade




8202WH/8235WH
8202BK/8235BK
PAR30 75W max.

Accessory holder: 8583

Accessories: Two AF3 Diffusion, ADF3 or AL3 series.

PAR16 Cylinder shade



8202WH/8216WH
8202BK/8216BK
PAR16 75W max.

Accessory holder: 8581

Accessories: Two AF2 or ADF2 series.
(60W max. w/accessories)

Note: Not for use with AL2HC

PAR20 Cylinder shade




8202WH/8226WH
8202BK/8226BK
PAR20 50W max.

Accessory holder: 8582

Accessories: Two AF25 diffusion,
ADF25 or AL25 series.

PAR30 Cylinder shade




8202WH/8236WH
8202BK/8236BK
PAR30 75W max.

Accessory holder: 8583

Accessories: Two AF3 diffusion, ADF3 or AL3 series.

PAR20 Ring shade




8202WH/8228WH
8202BK/8228BK
PAR20, 50W max.

Accessory holder: 8582

Accessories: Two AF25 diffusion,
ADF25 or AL25 series.

PAR30 Ring shade



8202WH/8238WH
8202BK/8238BK
PAR30 75W max.

Accessory holder: 8583

Accessories: Two AF3 diffusion, ADF3 or AL3 series.

PAR38 Ring shade



8202WH/8248WH
8202BK/8248BK
PAR38 150W max.

Accessory holder: 8595

Accessories: Two AF4, ADF4 series. (All)