DNG1206R5

Glazed doors | Floor Standing Enclosures

CONNECT AND PROTECT



H	1200
W	600
Item no.	DNG1206R5
VA h	976
VA w	415

Description: Glazed door with fitted clear safety glass to view the inside of the enclosure. Equipped with double-bit 3 mm lock system and door frame. Allows all options of the locking program. Compatible with combinable and compact enclosure ranges.

Material: Frame: 2 mm steel plate. Viewing area: 4 mm clear safety glass.

Finish: RAL 7035 structured powder coating.

Protection: Complies with IP 55 | TYPE 12 | IK 07.

Pack quantity: 1 piece.

Mounting requirements: Use hinge kit DNMK01 if no door was fitted previously.

Electrical components can be viewed while the door is closed, which keeps unauthorized personnel out and maintains the ingress protection.

IP 55 / IK 07