



Project: _____

Fixture Type: _____

Location: _____

Contact/Phone: _____

TRAC - LITES LOW VOLTAGE SERIES R701, R702, R731 and R740

PRODUCT DESCRIPTION

Socket Ceramic Bi-Pin.


Transformer 50VA 12V electronic transformer with circuit protection.

Aiming 90° vertical aiming capability and 358° rotation.

Adapter Copper alloy contacts provide precise spring action • True, positive electrical ground • Spring-loaded locking latch with embossed polarity arrows secures trac light to trac • Compatible with both Trac-Lites and Trac-Master Trac • "Pull-up" contact to up position for use on Trac-Master two-circuit trac.

Labels UL/CUL listed.

Specifications subject to change without notice.



Low Voltage MR16 Cylinder


Construction Polycarbonate transformer housing with a painted formed steel lamp housing.

Catalog Number	Finish	Lamp
R701 WH	White	12V, 20-50W MR16
R701 BL	Black	12V, 20-50W MR16

ACCESSORIES

Cat. No.	Description	Cat. No.	Description
CGF 200	Color Glass Filter	HCLBL 200	Hexagonal Cell Louver - Louver
DCCF 200	Dichroic Color Correction Filter	DIFF 200	Diffusion Glass Lens
DGF 200	Dichroic Glass Filter	UVF 200	UV Filter

See specification sheet [D1.2.2](#) for details.



Low Voltage MR16 Roundback


Construction Polycarbonate transformer housing with a painted formed steel lamp housing.

Catalog Number	Finish	Lamp
R702 WH	White	12V, 20-50W MR16
R702 BL	Black	12V, 20-50W MR16

ACCESSORIES

Cat. No.	Description	Cat. No.	Description	Cat. No.	Description
CGF 175	Color Glass Filter	HCLBL 175	Hexagonal Cell Louver - Louver	LSPREAD 175	Linear Spread Glass Lens
DCCF 175	Dichroic Color Correction Filter	DIFF 175	Diffusion Glass Lens	SOLITE 175	Uniformity Lens (Solite)
DGF 175	Dichroic Glass Filter	UVF 175	UV Filter	PRISM 175	Prismatic Spread Glass Lens

See specification sheet [D1.2.2](#) for details.




TRAC - LITES LOW VOLTAGE SERIES R701, R702, R731 and R740

Low Voltage MR16 Gimbal Ring

Construction Polycarbonate transformer housing with a painted formed steel lamp housing.

Catalog Number	Finish	Lamp
R731 WH	White	12V, 20-50W MR16
R731 BL	Black	12V, 20-50W MR16
R731 BZ	Bronze	12V, 20-50W MR16



ACCESSORIES


Cat. No.	Description	Cat. No.	Description	Cat. No.	Description
CGF 200	Color Glass Filter	HCLBL 200	Hexagonal Cell Louver - Louver	LSPREAD 200	Linear Spread Glass Lens
DCCF 200	Dichroic Color Correction Filter	DIFF 200	Diffusion Glass Lens	SOLITE 200	Uniformity Lens (Solite)
DGF 200	Dichroic Glass Filter	UVF 200	UV Filter	PRISM 200	Prismatic Spread Glass Lens

See specification sheet [D1.2.2](#) for details.

Low Voltage MR16 Pinchback

Construction Polycarbonate transformer housing with a painted die-cast aluminum lamp housing.

Catalog Number	Finish	Lamp
R740 WH	White	12V, 20-50W MR16
R740 BL	Black	12V, 20-50W MR16
R740 BZ	Painted Bronze	12V, 20-50W MR16



ACCESSORIES

Cat. No.	Description	Cat. No.	Description
CGF 200	Color Glass Filter	HCLBL 200	Hexagonal Cell Louver - Louver
DCCF 200	Dichroic Color Correction Filter	DIFF 200	Diffusion Glass Lens
DGF 200	Dichroic Glass Filter	UVF 200	UV Filter

See specification sheet [D1.2.2](#) for details.