

## Solenoid Voltage Testers

### Features




- Extremely rugged and reliable
- Vibrates when voltage is present
- Tests for AC Voltage
- Tests for DC Voltage
- Replaceable leads with shielded probe tips
- Bright, long-life LED's and neon indicator lamp
- Dual voltage indication for backup safety
- 2-year warranty

### Accessories

Includes	
Standard Test Leads	61-070
Optional	
Resistor-fused Leads*	61-072
Padded Nylon Case	C-90
Leather Case	61-010

\*Special, current-limiting resistor in each lead acts as a fuse to open in a short-circuit situation.



**61-065**

**Vol-Test® Voltage Tester**  
Tests from 100-600V AC/DC

**61-076**

**Vol-Con® Voltage/  
Continuity Tester**  
Automatic switching  
continuity tester, tests  
from 5-600V AC/DC



Solenoid Voltage Testers

## XL-Series Solenoid Voltage Testers

### Features



- Extremely rugged and reliable tester
- Vibrates when voltage is present
- Tests AC/DC Voltage
- Replaceable leads with shielded probe tips
- Bright, long-life LED's and neon indicator
- Dual voltage indication for backup safety
- Compact size
- 2-year warranty

### Accessories

Includes	
Standard Test Leads	TL-80
Optional	
Resistor-fused Leads*	TL-82
Padded Nylon Case	C-90
Leather Case	61-010

\*Special, current-limiting resistor in each lead acts as a fuse to open in a short-circuit situation.



**61-086**

**Vol-Con® XL  
Voltage/Continuity  
Tester**  
Audible continuity,  
audible voltage  
indication, tests from  
6-600V AC/DC

**61-085**

**Vol-Test® XL  
Voltage Tester**  
Tests from  
80-600V AC/DC



## Carrying Cases



**61-010**

Leather case for use with voltage testers

**61-020**  
Premium leather case for use with voltage testers



**C-290**

Nylon carrying case for use with DMM's



**C-90**

Nylon carrying case for use with all Vol-Con® and Vol-Test® Testers



**61-445**

Small nylon carrying case with four convenient pockets



**61-447**

Large nylon carrying case with six large inside pockets and one zippered outside pocket



## Carrying Case Selection Guide

MULTIMETER CARRYING CASE SELECTION GUIDE	320 Series			350			360		490		600 Series			610		630	
	61-320	61-322	61-324	61-350	61-352	61-354	61-360	61-361	61-494	61-495	61-602	61-603	61-609	61-610	61-614	61-633	61-635
C-290 Nylon Carrying Case	•	•	•	•	•	•	•	•	•	•	•	•	•			•	•

TESTER CARRYING CASE SELECTION GUIDE	Voltage Testers									
	61-058	61-065	61-076	61-085	61-086	61-090	61-092	61-681	61-682	61-164
61-010 Leather Tester Case		•	•							
61-020 Premium Leather Tester Case		•	•							
61-179 Nylon Carrying Case										•
C-50 Nylon Carrying Case	•									
C-90 Nylon Carrying Case		•	•	•	•	•	•	•	•	
C-954 Hard Carrying Case										•
C-958 Hard Carrying Case										•

CLAMP METER CARRYING CASE SELECTION GUIDE	61-452	700 Series			730		760 Series			770	
		61-701	61-702	61-704	61-732	61-736	61-764	61-766	61-768	61-772	61-774
61-179 Nylon Carrying Case					•	•					
C-452 Nylon Carrying Case	•										
C-700 Nylon Carrying Case		•	•	•							
C-730 Nylon Carrying Case					•	•					
C-760 Carrying Case							•	•	•		
C-770 Nylon Carrying Case										•	•