

## SecuriTEST™ CCTV/Security Tester

CCTV installers often need to carry a variety of testing tools to complete their work. SecuriTEST combines the most-needed tools in one easy-to-carry package. Since all connections (video/communications/DMM) attach to a single unit, SecuriTEST eliminates the need to juggle several devices while on a ladder or lift, making working conditions safer and increasing productivity.

- **Six Essential CCTV Tools** – Combines a CCTV video tester, PTZ camera controller, Digital Multi-Meter, UTP cable tester, video test pattern generator and PTZ protocol analyzer in a single compact package.
- **Save Time & Money** – Test, aim and focus cameras when working alone and save time by not having to walk back to the control center to verify functionality of each camera.
- **Compact Design** – Combines all the most needed—security tools in a lightweight, easy-to-carry unit with a sharp, bright 2.5in (6.3cm) color LCD screen with on-screen displays for PTZ control/diagnostics and DMM readouts.
- **PTZ Protocol Analyzer** – Compatible with over a dozen PTZ protocols to test and program cameras in the field. Decodes and identifies output from PTZ console to aid in troubleshooting.



| Description                           | Cat. No. |
|---------------------------------------|----------|
| SecuriTEST™ CCTV/Security Tester only | 33-891   |
| SecuriTEST™ Tester Pouch only         | 62-891   |

Includes: Rechargeable batteries, AC charger, car charger, test leads, wiremap terminator, neck strap and manual.



## VDV MultiMedia Cable Tester

Easy-to-use tester for installers working with voice, data and video applications. One tester for all applications!

- **Voice** – supports 3-pair USOC and 6-position RJ-11/12 jacks for telephone cable testing
- **Data** – supports both shielded and unshielded cable testing to T568A/B (RJ-45)
- **Video** – tests coax cable for opens and shorts with F-connector interface
- Tests for opens, shorts, miswires, reversals and split pairs. Also indicates correct wiremap. Has automatic shut off (to prolong battery life) and low battery indicator.
- Easy to read LCD display with “PASS/FAIL” indicator after each test
- Tone generator supports 4 different tones making fault isolation easier
- One remote wiremap and testing unit is stored inside tester— easier to keep all parts together
- Uniquely designed remote accommodates RJ-11, RJ-45 and F-style connectors

Integrated RJ11/12 (phone), RJ45 (UTP/STP) and Coax (F-Connector) interfaces on top of the unit

Compact ergonomic design puts full-featured VDV functionality in the palm of your hand.

Detachable remote with RJ11/12, RJ45 and Coax (F-Connector) interfaces. Stores securely in the base of the main unit for ready availability and easy patch cable testing.



Large LCD displays user current test mode, test results and all faults for the various cable types. Display automatically warns of voltage on lines and shows a Pass or Miswire message after each test.

Remote ID number (flashing) or “S” for shielded (flashing).

A single button push immediately selects between VOICE, DATA or VIDEO testing functions.

Pressing the TONE button starts “Instant-On” tone generator in the VOICE, DATA or VIDEO mode.

| Description                                | Cat. No. |
|--|----------|
| Kit with integrated remote and accessories | 33-856   |