

Data T®-Cutter

- Cuts round communication cable and maintains cable geometry for better cable performance
- Cuts multi-pair cable up to .500 in. (12.7mm) and coaxial cable up to RG-9/U
- Suitable for soft cables (not ACSR)
- Steel reinforced center conductors can be trimmed with bolt cutting holes
- Locking latch keeps tool closed in pouch
- Data T®-Cutter II designed for RG-58 and RG-6 coaxial cable



| Description | Cat. No. |
|-------------------|----------|
| Data T®-Cutter | 45-074 |
| Data T®-Cutter II | 45-075 |

D-Sub/Double-D Service Tool

- Exact replacement of the AMP open-barrel service tool for stamped contacts and D-Sub contacts
- Also crimps Double-D, high density, miniature contacts
- Includes openings for crimping insulated terminals and cutters for machine screws



| Description | Cat. No. |
|-----------------------------|----------|
| D-Sub/Double-D Service Tool | 30-426 |

Economy Round Cable and Wire Cutter

- Cuts multi-conductor cable up to .500 in. (12.7mm) and solid or stranded wire up to #8 AWG (10mm²)
- Built-in return spring, locking latch
- Stamped, hardened steel frame with curved cutting blades



| Description | Cat. No. |
|---|----------|
| Multi Conductor Cable to .500 in. (12.7mm) Solid or Stranded | 35-051 |

Center Conductor Cutter

- Trims coax center conductor to 3/16 in. (4.8 mm) length for proper installation into a dual crimp coax connector.



| Description | Cat. No. |
|-------------------------|----------|
| Center Conductor Cutter | 35-060 |

Lever™ -Snips Electrician's Scissors with Stripping Notches

- Ergonomic design gives added leverage
- Spring-action, mechanical advantage increases stripping leverage and reduces operator fatigue
- Double plated for added rust protection
- Extra-deep serrations grips wire better



| Description | Cat. No. |
|---|----------|
| Electrician's Scissors with Stripping Notches | 35-087 |

Cable Splicing Kit



35-093

| Description | Cat. No. |
|---|----------|
| Cable Splicing Kit (Scissors, Splicing Knife, Leather Holder) | 35-093 |
| Leather Holder only for Scissors and Knife | 35-094 |

Electrician's Scissors



35-090
Holder
Only



35-088

35-089

- Designed for use in telephone and electrical service applications
- Cut up to 16 AWG solid and 12 AWG stranded wire
- Serrated surface on back blade edge cleans wire
- Electrician's Scissors with stripping notches strip 19 and 23 AWG wire

| Description | Cat. No. |
|--|----------|
| Electrician's Scissors w/stripping notches | 35-088 |
| Electrician's Scissors | 35-089 |
| Leather Scissors Holder Only | 35-090 |

Cable Splicing Knife

- High carbon steel blade remains sharp and cuts easily through many insulation types
- Comfortable, full size, no slip handle for easy use



| Description | Cat. No. |
|---|----------|
| Cable Splicing Knife and Leather Holder | 35-091 |
| Leather Knife Holder Only | 35-092 |

Coaxial Selection Chart

Compression Style



| Cable | Cutter | Stripper | Crimper | Connector | Tester |
|----------------------|----------------|------------------------|--|--------------------------------|-----------------------------------|
| CATV/SATV/F-type | | | | | 33-856, 33-880 33-881, 33-887* |
| RG-59 | 45-074, 45-075 | 45-265, 45-603, 45-320 | 30-603, 30-793, 30-703, 30-720, 30-633 | 89-054, 89-104, 89-059, 89-159 | |
| RG-6 | 45-074, 45-075 | 45-262, 45-603, 45-320 | 30-603, 30-793, 30-703, 30-720, 30-633 | 89-055, 89-105,89-060, 89-160 | |
| RG-6 Quad Shield | 45-074, 45-075 | 45-282, 45-603, 45-320 | 30-603, 30-793, 30-703, 30-720, 30-633 | 89-056, 89-106, 89-060, 89-160 | |
| RG-6 & Quad 6 Plenum | 45-074, 45-075 | 45-510 | 30-603, 30-793, 30-703, 30-720, 30-633 | 89-060P, 89-160P | |
| RG-11 | 45-074, 45-075 | 45-164, 45-510 | 30-603, 30-793, 30-720 | 89-011 | |
| Minis | 45-074, 45-075 | 45-529 | 30-603, 30-793, 30-703 | 89-014SM, 89-014SMRCA | |
| BNC | | | | | |
| RG-59 | 45-074, 45-075 | 45-265, 45-603, 45-320 | 30-603, 30-793, 30-703 | 89-058, 89-5058 | |
| RG-6 | 45-074, 45-075 | 45-265, 45-603, 45-320 | 30-603, 30-793, 30-703 | 89-057, 89-5057 | |

Crimp Style



| Cable | Cutter | Stripper | Crimper | Connector | Tester |
|-------------------|----------------|------------------------|----------------|------------------------|-----------------------------------|
| CATV/SATV/F-Type | | | | | 33-856, 33-880 33-881, 33-887* |
| RG-59 | 45-074, 45-075 | 45-265, 45-603, 45-320 | 30-503 | 85-036, 85-016, 86-016 | |
| RG-6 | 45-074, 45-075 | 45-265, 45-603, 45-320 | 30-503 | 85-037, 85-017, 86-017 | |
| RG-6 Quad Shield | 45-074, 45-075 | 45-282, 45-603, 45-320 | 30-503 | 85-057, 85-030, 86-030 | |
| RG-6 Plenum | 45-074, 45-075 | 45-282, 45-603 | 30-503 | N/A | |
| RG-11 | 45-074, 45-075 | 45-164, 45-510 | N/A | N/A | |
| BNC | | | | | |
| RG-59, Non-Plenum | 45-074, 45-075 | 45-520 | 30-502, 30-483 | 85-513, 85-517, 85-502 | |
| RG-6 Non-Plenum | 45-074, 45-075 | 45-520 | 30-483 | 85-545 | |

*Need LA-4173 adapter.