



## Wire Marker Booklets



Wire Markers

- Convenient pocket-size booklets
- Plastic-impregnated cloth construction for long-lasting durability
- Resists abrasion, moisture, dirt and oil
- Perforated 1/4 in. x 1-1/2 in. markers can be separated into half-length sizes
- Non-smear black legend ensures high visibility
- Self-sticking on wire and cable
- For applications above or below ground

### Specifications:

Temperature Range: -40°F to 180°F (-40°C to 82°C)  
Adhesion: 45 oz./in. width ultimate

## Load Centers

- Contains common household legends — bedroom, living room, dryer, water heater, security system, etc.



| Description                     | Cat. No. |
|---------------------------------|----------|
| Load Center Wire Marker Booklet | 44-154   |

## Legend Assortments\*


| Legend  | Quantity   | Cat. No. |
|---|--|----------|
| 0-9   | 45 Markers each  | 44-101   |
| A-Z<br>0-15<br>+, -, /                                | 10 Markers each  | 44-102   |
| 1-45  | 10 Markers each  | 44-103   |
| 46-90   | 10 Markers each  | 44-104   |
| 1, 2, 3   | 150 Markers each   | 44-105   |
| A, B, C   | 150 Markers each   | 44-106   |
| A-Z**   | 45 Markers each  | 44-148   |
| T1, T2, T3  | 150 Markers each   | 44-107   |
| L1, L2, L3  | 150 Markers each   | 44-108   |
| 1-15<br>16-90<br>A-Z<br>+, -, /, 0                    | 6 Markers each<br>4 Markers each<br>2 Markers each<br>2 Markers each     | 44-109   |
| 1, 2, 3<br>A, B, C<br>T1, T2, T3<br>L1, L2, L3        | 45 Markers each<br>45 Markers each<br>30 Markers each<br>30 Markers each | 44-110   |
| +, -, AC, DC<br>POS, NEG, GND<br>NEUT<br>SPARE, BLANK | 45 Markers each<br>33 Markers each<br>27 Markers each<br>21 Markers each | 44-111   |

\*Ten pages per booklet with each page bearing the legend assortment indicated. All booklets (except 44-111) contain 450 wire markers and 450 terminal markers. Booklet 44-111 includes 348 wire markers and 348 terminal markers.

\*\*Booklet 44-148 contains 26 pages, one page of 45 markers per letter, 1170 total markers.

## Write-On Marker Booklets\*

- Use for developing personal identification systems
- Surface accepts pen, pencil or rubber stamp



| Marker Size* (Inches) | Markers per page | Pages per book | Cat. No. |
|-----------------------|------------------|----------------|----------|
| 1 x 2-1/2             | 6                | 10             | 44-151   |
| 1 x 5                 | 3                | 10             | 44-152   |

\*Write-on area for 2-1/2 in. markers is 3/4 in. x 1 in. Write-on area for 5 in. markers is 1 in. x 1 in. Adhesion: .25 oz./in. width ultimate