


Vol-Con® Elite Voltage Testers

Features



- Digital circuitry for better resolution
- Tests for AC Voltage from 24-600VAC
- Tests for DC Voltage from 6-220VDC
- Audible continuity
- Non-contact voltage indication
- Low impedance to eliminate ghost voltages
- Low battery indicator
- Replaceable silicone test leads
- Integral lead storage
- 2-year warranty



61-092
Vibration mode



61-090

Accessories

Includes	
Silicone Test Leads	TL-102
Optional	
Carrying Case	C-90



Vibration mode gives a tactile indication of the voltage level.



Non-contact voltage sensor easily locates breaks in power cords.



Carrying Cases



61-010
Leather case for use with voltage testers

61-020
Premium leather case for use with voltage testers



C-90
Nylon carrying case for use with all Vol-Con® and Vol-Test® Testers



C-290
Nylon carrying case for use with DMM's



61-445
Small nylon carrying case with four convenient pockets



61-447
Large nylon carrying case with six large inside pockets and one zippered outside pocket



Carrying Case Selection Guide

MULTIMETER CARRYING CASE SELECTION GUIDE	320 Series			350			360		490		600 Series			610		630	
	61-320	61-322	61-324	61-350	61-352	61-354	61-360	61-361	61-494	61-495	61-602	61-603	61-609	61-610	61-614	61-633	61-635
C-290 Nylon Carrying Case	•	•	•	•	•	•	•	•	•	•	•	•	•			•	•

TESTER CARRYING CASE SELECTION GUIDE	Voltage Testers													
	61-058	61-065	61-076	61-085	61-086	61-090	61-092	61-681	61-682	61-164	61-165	61-954	61-956	61-958
61-010 Leather Tester Case		•	•											
61-020 Premium Leather Tester Case		•	•											
61-179 Nylon Carrying Case										•	•			
C-50 Nylon Carrying Case	•													
C-90 Nylon Carrying Case		•	•	•	•	•	•	•	•					
C-954 Hard Carrying Case												•	•	
C-958 Hard Carrying Case														•

CLAMP METER CARRYING CASE SELECTION GUIDE	61-452	700 Series			730		760 Series			770	
		61-701	61-702	61-704	61-732	61-736	61-764	61-766	61-768	61-772	61-774
61-179 Nylon Carrying Case					•	•					
C-452 Nylon Carrying Case	•										
C-700 Nylon Carrying Case		•	•	•							
C-730 Nylon Carrying Case					•	•					
C-760 Carrying Case							•	•	•		
C-770 Nylon Carrying Case										•	•