


Push-Button Switches

- Great for household appliances, lamps and motor controls
- Available in normally open, normally closed and standard On-Off circuitry
- Wire leads are #18 AWG, 6" stripped wire
- 1/2 in. diameter mounting hole
- Bulk packaging of 100 available upon request



Product	Description	Actuator	Poles	Circuitry	Termination Style	No. of Terminals	Ratings	Dimensions (L" × W" × H")	Cat. No.
	Miniature Push-Button Switch*	Black Plastic	SPST	On-Off	Wire Lead	2	6 Amp 125VAC, 1 Amp 250VAC, 10 Amp 14VDC	.66 × .53 × .32	774082
	Round Body Push-Button Switch**	Black Plastic	SPST NO	(On)-Off	Screw	2	3/4 Amp 125VAC/DC, 1/4 Amp 250VAC/DC	.66 Dia. × 1.89	774083
	Round Body Push-Button Switch**	Black Plastic	SPST NC	On-(Off)	Screw	2	3/4 Amp 125VAC/DC, 1/4 Amp 250VAC/DC	.66 Dia. × 1.89	774084
	Momentary Contact Push-Button Switch	Black Plastic	SPST NO	(On)-Off	Screw	2	6 Amp 120VAC, 3 Amp 240VAC	.88 × .54 × .35	774022
	Momentary Contact Push-Button Switch	Red Plastic	SPST NC	On-(Off)	Screw	2	3 Amps 120VAC, 1.5 Amp 240VAC	.88 × .54 × .35	774023
	Maintained Contact Push-Button Switch	Black Plastic	SPST	On-Off	Wire Leads	2	8 Amp 125VAC/DC, 4 Amp 250VAC/DC, 10 Amp 125VAC, 1/3 HP 125VAC	.98 × .64 × .62	774021
	Maintained Contact Push-Button Switch*	Nickel Plated	SPST	On-Off	Wire Leads	2	6 Amp 125VAC, 3 Amp 250VAC	.97 × .80 × .36	774024
	Maintained Contact Push-Button Switch*	Brass Plated	SPST	On-Off	Wire Leads	2	6 Amp 125VAC, 3 Amp 250VAC	.97 × .80 × .36	774025
	Maintained Contact Push-Button Switch**	Nickel Plated	SPST	On-Off	Screw	2	6 Amp 125VAC/DC, 3 Amp 250VAC/DC	1.18 × .52 × .54	774080
1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1 1	Maintained Contact Push-Button Switch**	Nickel Plated	SPST	On-Off	Screw	2	15 Amp 125VAC, 10 Amp 250VAC	.92 × .66 × .46	774081
** BY 6. *	Momentary Contact Push-Button Switch**	Nickel Plated	SPST NO	(On)-Off	Screw	2	15 Amp 125VAC, 10 Amp 250VAC	1.38 × .58 × .60	774085
	Momentary Contact	Nieles Di L	ODOT NO	0- (00)	0-	0	15 Amp 125VAC.		774085BK†
	Push-Button Switch**	Nickel Plated	SPST NC	On-(Off)	Screw	2	10 Amp 250VAC	1.38 × .58 × .60	774086

^{**} **91**° **©** *c**91**° us

†Bulk Package of 100

() Denotes momentary action

