

## Variable-Speed Wall Controls

### Model CFVS-1N

- Variable speed control
- 10.1 amps
- Unlimited fan motor speeds



### Model 57W, 57V (3-Amp)\*

- 120V, 3 amps
- Fits single-gang box
- Positive on/off action—dial for variable selection of air speeds and sound levels
- Built-in radio noise suppressor
- Controls available in White (W) or Ivory (V)



### Model 72W, 72V

- 120V, 6 amps
- Other features same as 57W / 57V



## Single-Function Wall Controls

### Model DH100W

- Dehumidistat with variable setting from 20–80% relative humidity
- Dual voltage 24V/120V



## Timed Wall Controls

### Model CFT-12WH

- 12-hour time switch
- Rotary dial
- 20 amps



### Model VS-62WH

- 60-minute time switch
- For all NuTone heaters and fans except Pull-Chain type
- 20 amps



### Model VS-63WH

- 15-minute time
- For all NuTone heaters and fans except Pull-Chain type
- 20 amps



## Timed Wall Controls

### Model VS-66WH

- 60-minute timer
- Separate on/off control
- For two-gang outlet box
- Timer controls any NuTone heater or Ventilator
- On/Off section can be used for a separate light, vent or heater



### Model VS-67WH

- 60-minute timer
- Separate on/off controls
- For two-gang outlet box
- Timer section may control any NuTone heater or Ventilator
- On/Off section can be used for a separate light, vent or heater



### Model VS-68WH

- 15-minute timer
- Separate on/off control
- For two-gang outlet box
- Timer controls any NuTone heater or Ventilator
- On/Off section can be used for a separate light, vent or heater.



### Model VS-69WH

- 15-minute timer
- Separate on/off controls
- For two-gang outlet box
- Timer controls any heater or Ventilator
- On/Off section can be used for a separate light, vent or heater



## Attic Humidity Control

### Model HU100

- For use with attic ventilator models 350, 355, 356, 358 and RF-49BR
- For single-gang outlet box
- 120V / 6.0 amps



## Multi-Function / Lighted Controls

### Model 68W, 68V, P68W

- Two-Function Controls
- Two independent, 120V, 15 amp rocker switches (20 amps total)
- Fits single-gang box
- Controls available in White (W) or Ivory (V)
- Blister pack available, P68W



### Model 66W, 66V, P66W

- Three-Function Controls
- Three independent, 120V, 15 amp rocker switches (20 amps total)
- Fits single-gang opening
- Controls available in White (W) or Ivory (V)
- Blister pack available, P66W



### Model 77DW, 77DV, P77DW

- Four-Function Controls
- Single switch provides three settings for fan sensor (On-Auto-Off) on Sensing models
- Remaining switches for light/nightlight
- Works with QTX110HL heater/fan/light/nightlight
- Controls available in White (W) or Ivory (V)
- Fits single-gang opening
- Blister pack available, P77DW



### Model 69WL, 69VL

- Single-Function Controls
- For use with Ultra Silent™ Series fan units, or Remote In-Line Ventilators
- 120V, 20 amps
- Red light lets you know power is on
- Controls available in White (W) or Ivory (V)



### Model P59W

- 60-minute timer with "continuous on" feature
- Fits single gang box
- 120V / 20 amp or 240V / 10 amp

