


Series System

superior multiroom
audio starts here



C-Series MCA-C5

8 source/8 zone controller with built in RDS AM/FM tuner 40 watt x 2 channel digital amp zones 1-6. Apple app available for easy wireless control expandable up to 48 zones in the home.

All the power and flexibility you'll ever need are found in Russound "audio everywhere" systems and components. None more exemplary than the C5. Start here and build your customers' dream whole-house solution. Add your choice of keypad and wireless user interface apps. It's all here. Take a look.



Acclaim Thin Bezel Speakers




RSA-61
15° Angled 2-Way Ceiling Speaker
Recommended Power:
5-80 Watts
Tweeter:
1" Pivoting PEI
Woofers:
6 1/2" Vacuum Form Polypropylene

RSF-61
2-Way Ceiling Speaker
Recommended Power:
5-80 Watts
Tweeter:
3/4" Pivoting PEI
Woofers:
6 1/2" Vacuum Form Polypropylene




RSA-62
15° Angled 2-Way Ceiling Speaker
Recommended Power:
5-100 Watts
Tweeter:
1" Pivoting Silk - Ferrofluid Cooled
Woofers:
6 1/2" IMPP Ribbed Cone

RSF-62
2-Way Ceiling Speaker
Recommended Power:
5-90 Watts
Tweeter:
1" Pivoting Silk - Ferrofluid cooled
Woofers:
6 1/2" Polypropylene Cone




RSA-63
15° Angled 2-Way Ceiling Speaker
Recommended Power:
5-120 Watts
Tweeter:
1" Pivoting Teteron - Ferrofluid Cooled
Woofers:
6 1/2" Kevlar

RSF-63
2-Way Ceiling Speaker
Recommended Power:
5-100 Watts
Tweeter:
1" Pivoting Silk - Ferrofluid Cooled
Woofers:
6 1/2" IMPP Ribbed Cone



RSF-61T
Single-Point, Dual Voice Coil, Twin
Tweeter Ceiling Speaker
Recommended Power:
5-120 Watts
Tweeter:
2 x .75" Pivoting Silk - Ferrofluid cooled
Woofers:
6 1/2" IMPP Ribbed Cone

RSF-64
2-Way Ceiling Speaker
Recommended Power:
5-120 Watts
Tweeter:
1" Pivoting Teteron - Ferrofluid Cooled
Woofers:
6 1/2" Kevlar



Round Grill
3175-534287 RSG-R round

Square Grill
3175-533990 RSG-S square



audio
everywhere

2013 Featured Products