

# IEC Manual Motor Starters Enclosures and Enclosure Accessories

### Enclosures (Non-metallic)

#### For Surion Toggle Operated (GPS1BSAA-GPS1BSAP) Starters to 25 Amps

Enclosures will accommodate starters with 1 auxiliary or alarm contact on the left side and 1 auxiliary contact, shunt trip or undervoltage release (with or without early make contacts) on the right side. UL Listed for use with 1/2" NPT fittings.

For Use With	Mounting	Enclosure Type	Product Number	List Price GO-10A2C
GPS1BSAA-AP	Flush Panel	NEMA Type 1/IP41	GPEF41A	\$35.00
GPS1BSAA-AP	Flush Panel	NEMA Type 3R/12/IP55	GPEF55A	\$50.00
GPS1BSAA-AP	Surface	NEMA Type 1/IP41	GPES41A	\$30.00
GPS1BSAA-AP	Surface	NEMA Type 3R/12/IP55	GPES55A	\$45.00



GPEF\_\_A/GPES\_\_A Non-Metallic Enclosure

### Enclosure Accessories (Non-metallic)

For Use With	Enclosure Accessory Type	Product Description	Product Number	List Price GO-10A2C
GPS1BSAA-GPS1BSAP	Padlocking Device	Accepts up to 3 padlocks with hasps of .15-.31 inches (4-8 mm)	GPEPA	\$18.00
GPS1BSAA-GPS1BSAP	External Mushroom Head Push Button	Momentary	GPEPMA	\$24.00
GPS1BSAA-GPS1BSAP	External Mushroom Head Push Button	Push-to-stop/Turn-to-release	GPEPLA	\$35.00
GPS1BSAA-GPS1BSAP	External Mushroom Head Push Button	Push-to-stop/Key-to-release	GPEPKA	\$85.00
GPS1BSAA-GPS1BSAP	Conversion Kit	Converts Type 1 to 3R/12 (IP44 to IP55)	GPECA	\$12.00
GPS1BSAA-GPS1BSAP	Neutral Kit	—	GPENA	\$5.00
GPS1BSAA-GPS1BSAP	Adapter	Adapts enclosure to Type 3R/12 (IP55) to accommodate starter with undervoltage release with early make contacts	GPEUTA	\$6.00
GPS1BSAA-GPS1BSAP	Indicating Lights	Green 110-220V	GPELGAJ	\$18.00
GPS1BSAA-GPS1BSAP	Indicating Lights	Green 220-240V	GPELGAN	\$18.00
GPS1BSAA-GPS1BSAP	Indicating Lights	Green 380-440V	GPELGAU	\$18.00
GPS1BSAA-GPS1BSAP	Indicating Lights	Green 480-500V	GPELGAX	\$18.00
GPS1BSAA-GPS1BSAP	Indicating Lights	Green 600V	GPELGAY	\$18.00
GPS1BSAA-GPS1BSAP	Indicating Lights	Red 110-220V	GPELRAJ	\$18.00
GPS1BSAA-GPS1BSAP	Indicating Lights	Red 220-240V	GPELRAN	\$18.00
GPS1BSAA-GPS1BSAP	Indicating Lights	Red 380-440V	GPELRAU	\$18.00
GPS1BSAA-GPS1BSAP	Indicating Lights	Red 480-500V	GPELRAX	\$18.00
GPS1BSAA-GPS1BSAP	Indicating Lights	Red 600V	GPELRAY	\$18.00
GPS1BSAA-GPS1BSAP	Indicating Lights	Transparent 110-220V	GPELCAJ	\$18.00
GPS1BSAA-GPS1BSAP	Indicating Lights	Transparent 220-240V	GPELCAN	\$18.00
GPS1BSAA-GPS1BSAP	Indicating Lights	Transparent 380-440V	GPELCAU	\$18.00
GPS1BSAA-GPS1BSAP	Indicating Lights	Transparent 480-500V	GPELCAX	\$18.00
GPS1BSAA-GPS1BSAP	Indicating Lights	Transparent 600V	GPELCAY	\$18.00



GPEPA Padlocking Device



GPEP\_\_Mushroom Head Push Button



GPECA Conversion Kit

### Reference Publications

Instructions for non-metallic enclosures:

DEH-40283



GPENA Neutral Kit



GPEUTA Adapter



GPEL\_A\_Indicating Lights



**Publications and Reference:** See Section 17 for a complete list of additional product-related publications